



SMA Male to SMA Female Low Loss Test Cable 150 CM Length Using PE-P142LL Coax, RoHS

TECHNICAL DATA SHEET

PE340-150CM

The PE340's high performance test cable's 0.195 inch diameter and 83% phase velocity offer very low loss performance up to 18 GHz. The durable stainless steel connectors and FEP jacket provide a cost effective design ideal for test environments where a rugged cable assembly is required. The series is offered with Type N, TNC, and SMA connectors all rated to 18 GHz. A heavy Duty boot provides improved strain relief and adds to the durability of the cable assemblies. These cable assemblies are built using a double shielded flexible cable, providing excellent shielding effectiveness of greater than 95 dB. All PE340 cable assemblies are 100% Continuity, Hi-POT, and RF tested to published specifications. Custom lengths are built to order and shipped same day.

where a rugged cable assembly is required. The series is A heavy Duty boot provides improved strain relief and add are built using a double shielded flexible cable, providing cable assemblies are 100% Continuity, Hi-POT, and RF t and shipped same day.	s to the durability of the cable as excellent shielding effectivenes
 83% Velocity of Propagation Shielding effectiveness > 95 dB Maximum VSWR is < 1.35:1 to 18 GHz Minimum Bend Radius of 1.5 inches Operating Temperature range of -55 to +125 °C ROHS and REACH Compliant Same day shipment of custom lengths 100% Continuity, Hi-Pot, and RF tested 	
Configuration	
Connector 1	SMA Male
Connector 2	SMA Female
Cable Type	PE-P142LL
Electrical Specifications	
Frequency Range, GHz	DC to 18
Impedance, Ohms	50
Maximum VSWR	1.35:1
Velocity of Propagation, % RF Shielding, dB	83 95
	00
Typical Performance by Frequency	
Frequency 1	400
Frequency, MHz Insertion Loss	0.045 dB [0.15 dB]
Power Handling, KWatts	1.2
Frequency 2 Frequency, MHz	1000
Insertion Loss	0.072 dB [0.24 dB]
Power Handling, Watts	700
Frequency 3 Frequency, GHz	2
Insertion Loss	2 0.103 dB [0.34 dB]
Power Handling, Watts	500
0,	
Click the following link (or enter part number in "SEA	
inventory and certifications: SMA Male to SMA Femal	e Low Loss Test Cable 150 CM

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Low Loss Test Cable 150 CM Length Using PE-P142LL Coax, RoHS PE340-150CM

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to SMA Female Low Loss Test Cable 150 CM Length Using PE-P142LL Coax, RoHS

TECHNICAL DATA SHEET

- **Frequency 4** Frequency, GHz Insertion Loss Power Handling, Watts
- Frequency 5 Frequency, GHz Insertion Loss Power Handling, Watts

Frequency 6 Frequency, GHz Insertion Loss Power Handling, Watts

Frequency 7 Frequency, GHz Insertion Loss Power Handling, Watts

Electrical Specification Notes:

Mechanical Specifications

Cable Cable Type No of Shields Dielectric Type Jacket Material Cable Color Jacket Diameter, in [mm]

Connector 1

Type Connector 1 Specification Configuration Inner Conductor Material and Plating Inner Conductor Plating Specification Coupling Nut Material and Plating Coupling Nut Plating Specification Hex Size, Inch Torque, in-lbs [Nm] Body Material and Plating Body Plating Specification



PE340-150CM

3 0.127 dB [0.42 dB] 400

5 0.166 dB [0.54 dB] 300

10 0.24 dB [0.79 dB] 220

18 0.33 dB [1.08 dB] 160

Power handling values are calculated based on Cable properties. Power handling will vary based on the actual VSWR of the cable assembly.

PE-P142LL 3 PTFE FEP Green 0.195 [4.95]

SMA Male MIL-STD-348, Fig 310-1 Straight Beryllium Copper, Gold ASTM-B488 50µ In. Minimum Passivated Stainless Steel SAE-AMS-2700 5/16 8 [0.9] Passivated Stainless Steel SAE-AMS-2700

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Low Loss Test Cable 150 CM Length Using PE-P142LL Coax, RoHS PE340-150CM

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to SMA Female Low Loss Test Cable 150 CM Length Using PE-P142LL Coax, RoHS

TECHNICAL DATA SHEET



PE340-150CM

Dielectric Type	PTFE
Connector 2	
Туре	SMA Female
Configuration	Straight
Inner Conductor Material and Plating	Beryllium Copper, Gold
Inner Conductor Plating Specification	ASTM-B488, 50µ In. Minimum
Outer Conductor Material and Plating	Passivated Stainless Steel
Outer Conductor Plating Specification	SAE-AMS-2700
Body Material and Plating	Passivated Stainless Steel
Body Plating Specification	SAE-AMS-2700
Dielectric Type	PTFE
Temperature	
Temperature Operating Range, deg C	-55 to +125
Size	
Length, in [cm]	59.055 [150]
Diameter, in [mm]	0.37 [9.4]
Weight, lbs [g]	0.252 [114.31]
Repeated Minimum Bend Radius, in [mm]	1 [25.4]
Compliance Certifications (visit www.Pasternack.com RoHS Compliant	
REACH Compliant	Yes 07/19/2006
REACT Compliant	0//19/2000
Plotted and Other Data	
Notes:	Values at 25 °C, sea level
SMA Male to SMA Female Low Loss Test Cable 150 CM I	angth Using PE P142LL Copy, PoHS from Pastornack
	rnational orders. Our RF, microwave and fiber optic products
naintain a 99% availability and are part of the broadest se	
	blocker in the inductry.
Click the following link (or enter part number in "SEARCH"	on website) to obtain additional part information including price,
nventory and certifications: SMA Male to SMA Female Lo	w Loss Test Cable 150 CM Length Using PE-P142LL Coax, RoH
PE340-150CM	
JRL: http://www.pasternack.com/sma-male-sma-female-p	pe-p142II-cable-assembly-pe340-150cm-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com PE340-150CM CAD Drawing SMA Male to SMA Female Low Loss Test Cable 150 CM

Length Using PE-P142LL Coax, RoHS

