



SMA Male to SMA Female Low Loss Test Cable 60 Inch Length Using PE-P142LL Coax, RoHS

TECHNICAL DATA SHEET

PE340-60

The PE340's high performance test cable's 0.195 inch diameter and 83% phase velocity offer very low loss performance up to 18 GHz. The durable stainless steel connectors and FEP jacket provide a cost effective design ideal for test environments where a rugged cable assembly is required. The series is offered with Type N, TNC, and SMA connectors all rated to 18 GHz. A heavy Duty boot provides improved strain relief and adds to the durability of the cable assemblies. These cable assemblies are built using a double shielded flexible cable, providing excellent shielding effectiveness of greater than 95 dB. All PE340 cable assemblies are 100% Continuity, Hi-POT, and RF tested to published specifications. Custom lengths are built to order and shipped same day.

• 83% Velocity of Propagation Shielding effectiveness > 95 dB • Maximum VSWR is < 1.35:1 to 18 GHz • Minimum Bend Radius of 1.5 inches Operating Temperature range of -55 to +125 °C · ROHS and REACH Compliant Same day shipment of custom lengths 100% Continuity, Hi-Pot, and RF tested Configuration Connector 1 Connector 2 Cable Type **Electrical Specifications** Frequency Range, GHz Impedance, Ohms Maximum VSWR Velocity of Propagation, % RF Shielding, dB Typical Performance by Frequency **Frequency 1** Frequency, MHz Insertion Loss

Frequency 2 Frequency, MHz Insertion Loss Power Handling, Watts

Power Handling, KWatts

Frequency 3 Frequency, GHz Insertion Loss Power Handling, Watts 83 95

SMA Male

PE-P142LL

DC to 18

50

1.35:1

SMA Female

400 0.045 dB [0.15 dB] 1.2

1000 0.072 dB [0.24 dB] 700

2 0.103 dB [0.34 dB] 500

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Low Loss Test Cable 60 Inch Length Using PE-P142LL Coax, RoHS PE340-60

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to SMA Female Low Loss Test Cable 60 Inch Length Using PE-P142LL Coax, RoHS

TECHNICAL DATA SHEET

- Frequency, GHz Insertion Loss Power Handling, Watts
- Frequency 5 Frequency, GHz Insertion Loss Power Handling, Watts

Frequency 6 Frequency, GHz Insertion Loss Power Handling, Watts

Frequency 7 Frequency, GHz Insertion Loss Power Handling, Watts

Electrical Specification Notes:

Mechanical Specifications

Cable Cable Type No of Shields Dielectric Type Jacket Material Cable Color Jacket Diameter, in [mm]

Connector 1

Type Connector 1 Specification Configuration Inner Conductor Material and Plating Inner Conductor Plating Specification Coupling Nut Material and Plating Coupling Nut Plating Specification Hex Size, Inch Torque, in-lbs [Nm] Body Material and Plating Body Plating Specification



PE340-60

3 0.127 dB [0.42 dB] 400

5 0.166 dB [0.54 dB] 300

10 0.24 dB [0.79 dB] 220

18 0.33 dB [1.08 dB] 160

Power handling values are calculated based on Cable properties. Power handling will vary based on the actual VSWR of the cable assembly.

PE-P142LL 3 PTFE FEP Green 0.195 [4.95]

SMA Male MIL-STD-348, Fig 310-1 Straight Beryllium Copper, Gold ASTM-B488 50µ In. Minimum Passivated Stainless Steel SAE-AMS-2700 5/16 8 [0.9] Passivated Stainless Steel SAE-AMS-2700

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Low Loss Test Cable 60 Inch Length Using PE-P142LL Coax, RoHS PE340-60

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



SMA Male to SMA Female Low Loss Test Cable 60 Inch Length Using PE-P142LL Coax, RoHS

TECHNICAL DATA SHEET



PE340-60

PTFE
SMA Female Straight Beryllium Copper, Gold ASTM-B488, 50µ In. Minimum Passivated Stainless Steel SAE-AMS-2700 Passivated Stainless Steel SAE-AMS-2700 PTFE
-55 to +125
60 [152.4] 0.37 [9.4]
0.126 [57.15] 1 [25.4]
or current document) Yes 07/19/2006
Values at 25 °C, sea level
gth Using PE-P142LL Coax, RoHS from Pasternack Enterprises s. Our RF, microwave and fiber optic products maintain a 99% stry.
n website) to obtain additional part information including price, Loss Test Cable 60 Inch Length Using PE-P142LL Coax, RoHS
p142II-cable-assembly-pe340-60-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com PE340-60 CAD Drawing SMA Male to SMA Female Low Loss Test Cable 60 Inch

Length Using PE-P142LL Coax, RoHS

