



## SMA Male to SMA Male Cable 6 Inch Length Using PE-SR047FL Coax, RoHS

### RF Cable Assemblies Technical Data Sheet


PE34186LF-6

#### Configuration

- Connector 1: SMA Male
- Connector 2: SMA Male
- Cable Type: PE-SR047FL

#### Features

- Max Frequency 12.4 GHz



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE34186LF-6 SMA male to SMA male 6 inch cable using PE-SR047FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack SMA to SMA cable assembly has a male to male gender configuration with 50 ohm formable PE-SR047FL coax. The PE34186LF-6 SMA male to SMA male cable assembly operates to 12.4 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable 6 Inch Length Using PE-SR047FL Coax, RoHS PE34186LF-6](#)



SMA Male to SMA Male Cable 6 Inch Length  
Using PE-SR047FL Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE34186LF-6

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR			1.4:1	
Capacitance		32 [104.99]		pF/ft [pF/m]

**Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	10	12.4	GHz
Insertion Loss (Typ.)	0.379	0.524	0.629	0.839	0.921	dB

**Mechanical Specifications**

**Cable Assembly**

Length*	6 in [152.4 mm]
Diameter	0.312 in [7.92 mm]
Weight	0.015 lbs [6.8 g]

**Cable**

Cable Type	PE-SR047FL
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
Jacket Diameter	0.047 in [1.19 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable 6 Inch Length Using PE-SR047FL Coax, RoHS PE34186LF-6](#)



SMA Male to SMA Male Cable 6 Inch Length  
Using PE-SR047FL Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE34186LF-6

**Connectors**

Description	Connector 1	Connector 2
Type	SMA Male	SMA Male
Specification	MIL-STD-348	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	50µ in. minimum	50µ in. minimum
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Gold	Brass, Gold
Body Plating Specification	50µ in. minimum	50µ in. minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	50µ in. minimum	50µ in. minimum
Hex Size	5/16 in	5/16 in
Torque	5 in-lbs [0.57 Nm]	5 in-lbs [0.57 Nm]

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable 6 Inch Length Using PE-SR047FL Coax, RoHS PE34186LF-6](#)



SMA Male to SMA Male Cable 6 Inch Length  
Using PE-SR047FL Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE34186LF-6

**How to Order**

Part Number Configuration:

**PE34186LF - xx uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE34186LF-12 = 12 inches long cable  
PE34186LF-100cm = 100 cm long cable

SMA Male to SMA Male Cable 6 Inch Length Using PE-SR047FL Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable 6 Inch Length Using PE-SR047FL Coax, RoHS PE34186LF-6](https://www.pasternack.com/sma-male-sma-male-pe-sr047fl-cable-assembly-pe34186lf-6-p.aspx)


URL: <https://www.pasternack.com/sma-male-sma-male-pe-sr047fl-cable-assembly-pe34186lf-6-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE34186LF-6 CAD Drawing

SMA Male to SMA Male Cable 6 Inch Length Using PE-SR047FL Coax, RoHS

Standard Lengths	
-12	12"
-24	24"
-36	36"
-48	48"
-60	60"
-XXX	Custom Length in Inches



NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].  
 4. LENGTH TOLERANCE IS  $\pm 1.5\%$  OR  $3/8"$ , WHICHEVER IS GREATER.

DWG TITLE  
**PE34186LF-XX**

**PE PASTERNAK®**  
 Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com

REV. A	FSCM NO. 53919	CAD FILE 012508	SCALE N/A	SIZE A	127
--------	----------------	-----------------	-----------	--------	-----