

## SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink



### RF Cable Assemblies Technical Data Sheet



**PE34246/HS**

#### Configuration

- Connector 1: SMA Male
- Connector 2: TNC Male
- Cable Type: RG316-DS

#### Features

- Max Frequency 3 GHz
- Shielding Effectivity > 85 dB
- 69.5% Phase Velocity
- Double Shielded
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE34246/HS SMA male to TNC male cable using RG316-DS coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to TNC cable assembly has a male to male gender configuration with 50 ohm flexible RG316-DS coax. The PE34246/HS SMA male to TNC male cable assembly operates to 3 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 85 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink PE34246/HS](#)



## SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink

### RF Cable Assemblies Technical Data Sheet

**PE34246/HS**

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
RF Shielding	85			dB
Capacitance		28.96 [95.01]		pF/ft [pF/m]
DC Resistance Inner Conductor		83.82 [275]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		5.33 [17.49]		Ω/1000ft [Ω/Km]
Operating Voltage (AC)			335	Vrms

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.109	0.159	0.238	0.379	0.579	dB/ft
	0.36	0.52	0.78	1.24	1.9	dB/m

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the straight connector.

#### Mechanical Specifications

##### Cable Assembly

Weight 0.055 lbs [24.95 g]

##### Cable

Cable Type	RG316-DS
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.114 in [2.9 mm]
One Time Minimum Bend Radius	0.59 in [14.99 mm]
Repeated Minimum Bend Radius	1.57 in [39.88 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink PE34246/HS](#)

## SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink



### RF Cable Assemblies Technical Data Sheet

**PE34246/HS**

#### Connectors

Description	Connector 1	Connector 2
Type	SMA Male	TNC Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 $\mu$ in minimum	30 $\mu$ in. minimum
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 $\mu$ in minimum	100 $\mu$ in. minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 $\mu$ in minimum	
Hex Size	5/16 inch	
Torque	3 in-lbs [0.34 Nm]	

#### Environmental Specifications

##### Temperature

Operating Range

-55 to +165 deg C

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink PE34246/HS](#)

## SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink



### RF Cable Assemblies Technical Data Sheet

**PE34246/HS**

#### How to Order

Part Number Configuration:



Example: PE34246/HS-12 = 12 inches long cable  
PE34246/HS-100cm = 100 cm long cable

SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink PE34246/HS](#)


URL: <https://www.pasternack.com/sma-male-straight-to-tnc-male-cable-using-rg316-ds-with-heatshrink-pe34246-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE34246/HS CAD Drawing

## SMA Male to TNC Male Cable Using RG316-DS Coax with HeatShrink

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	01/25/2023	BPUCHASKI	AGANWANI



**NOTES:**

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS , ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.

 <b>PASTERNAK®</b> an INFINIT® brand				INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5		REV A								
				SCALE	NONE	1 OF 1								
				DESCRIPTION	SHEET									
		<a href="http://www.Pasterнак.com">www.Pasterнак.com</a> Phone: 1.866.727.8376   1.949.261.1920												
<p>OTHERWISE SPECIFIED DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS</p> <p>TOLERANCES:</p> <table border="1"> <tr> <td>FRACTIONS</td> <td><math>\pm 1/32</math></td> </tr> <tr> <td>ANGLES <math>\pm 1^\circ</math></td> <td></td> </tr> <tr> <td>LENGTH TOLERANCES:</td> <td></td> </tr> <tr> <td>2 [ .5 ]</td> <td><math>\pm 0.06</math> [ .13 ]</td> </tr> </table>		FRACTIONS	$\pm 1/32$	ANGLES $\pm 1^\circ$		LENGTH TOLERANCES:		2 [ .5 ]	$\pm 0.06$ [ .13 ]			<p>ITEM NO.</p> <p>PE34246/HS</p>		
FRACTIONS	$\pm 1/32$													
ANGLES $\pm 1^\circ$														
LENGTH TOLERANCES:														
2 [ .5 ]	$\pm 0.06$ [ .13 ]													
<p><math>\pm 1/12</math> [ .035 ] <math>\pm 0.06</math> [ .13 ]</p> <p><math>\pm 1/12</math> [ .035 ] <math>\pm 0.06</math> [ .13 ]</p> <p><math>\pm 1/12</math> [ .035 ] <math>\pm 0.06</math> [ .13 ]</p> <p><math>\pm 1/12</math> [ .035 ] <math>\pm 0.06</math> [ .13 ]</p>		<p>DRAWN BY</p> <p>BPUCHASKI</p>		<p>SIZE</p> <p>A</p>										
<p><math>\pm 1/12</math> [ .035 ] <math>\pm 0.06</math> [ .13 ]</p> <p><math>\pm 1/12</math> [ .035 ] <math>\pm 0.06</math> [ .13 ]</p> <p><math>\pm 1/12</math> [ .035 ] <math>\pm 0.06</math> [ .13 ]</p> <p><math>\pm 1/12</math> [ .035 ] <math>\pm 0.06</math> [ .13 ]</p>		<p>CAGE CODE</p> <p>53919</p>		<p>DIMENSIONS ARE FOR REFERENCE ONLY NOT TO CHANGE WITHOUT NOTICE</p>										
<p><math>&gt;300</math> [ 7620 ]</p>														