

75 Ohm BNC Male to 75 Ohm SMC Plug Right Angle Cable Using 75 Ohm RG179 Coax with HeatShrink



PE34329/HS

Configuration

- Connector 1: BNC Male
- Connector 2: SMC Plug Right Angle
- Cable Type: RG179
- Coax Flex Type: Flexible

Features

- 70% Phase Velocity
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE34329/HS 75 ohm BNC male to 75 ohm SMC plug right angle cable using 75 ohm RG179 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack BNC to SMC cable assembly has a male to plug gender configuration with 75 ohm flexible RG179 coax. The right angle SMC interface on the RG179 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		70		%
Capacitance		19.4 [63.65]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.046 lbs [20.87 g]

Cable

Cable Type	RG179
Impedance	75 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan

75 Ohm BNC Male to 75 Ohm SMC Plug Right Angle Cable Using 75 Ohm RG179 Coax with HeatShrink



PE34329/HS

Jacket Diameter	0.1 in [2.54 mm]
Repeated Minimum Bend Radius	0.4 in [10.16 mm]

Connectors

Description	Connector 1	Connector 2
Type	BNC Male	SMC Plug Right Angle
Specification		MIL-STD-348
Impedance	75 Ohms	75 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Brass, Gold	Gold
Contact Plating Specification	30 µin minimum	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	QQ-N-290
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 µin minimum	
Hex Size		11/32 inch
Torque		3 in-lbs 0.34 Nm

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

75 Ohm BNC Male to 75 Ohm SMC Plug Right Angle Cable Using 75 Ohm RG179 Coax with HeatShrink



PE34329/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE34329/HS - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE34329/HS-12 = 12 inches long cable
PE34329/HS-100cm = 100 cm long cable

75 Ohm BNC Male to 75 Ohm SMC Plug Right Angle Cable Using 75 Ohm RG179 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm BNC Male to 75 Ohm SMC Plug Right Angle Cable Using 75 Ohm RG179 Coax with HeatShrink PE34329/HS](https://www.pasternack.com/75-ohm-bnc-male-to-75-ohm-smc-plug-right-angle-cable-using-rg179-with-heatshrink-pe34329-hs-p.aspx)

URL: <https://www.pasternack.com/75-ohm-bnc-male-to-75-ohm-smc-plug-right-angle-cable-using-rg179-with-heatshrink-pe34329-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE34329/HS CAD Drawing

75 Ohm BNC Male to 75 Ohm SMC Plug Right Angle Cable Using 75 Ohm RG179 Coax with HeatShrink

