

TNC Male to TNC Male Cable Using RG188 Coax with HeatShrink

PE3434/HS




Configuration

- Connector 1: TNC Male
- Connector 2: TNC Male
- Cable Type: RG188
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- PTFE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3434/HS TNC male to TNC male cable using RG188 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to TNC cable assembly has a male to male gender configuration with 50 ohm flexible RG188 coax. The PE3434/HS TNC male to TNC male cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	

Specifications by Frequency

TNC Male to TNC Male Cable Using RG188 Coax with HeatShrink



PE3434/HS

Part Number	Length	Description	F1	Units	Weight (lbs)
		Frequency	400	MHz	
PE3434/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.2	dB/ft	
			0.66	dB/m	
PE3434/HS-12	12 inch	Insertion Loss (Typ.)	0.4	dB	0.08
PE3434/HS-24	24 inch	Insertion Loss (Typ.)	0.6	dB	0.091
PE3434/HS-36	36 inch	Insertion Loss (Typ.)	0.8	dB	0.101
PE3434/HS-48	48 inch	Insertion Loss (Typ.)	1	dB	0.111
PE3434/HS-72	72 inch	Insertion Loss (Typ.)	1.4	dB	0.131

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
 Loss due to Connector 2: 0.1 dB
 Base Weight: 0.08 pounds
 Additional Weight per Inch: 0.00084 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]
 Weight 0.07 lbs [31.75 g]

Cable

Cable Type RG188
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper Clad Steel, Silver
 Dielectric Type PTFE
 Number of Shields 1
 Shield Layer 1 Silver Plated Copper Braid
 Jacket Material PTFE, White
 Jacket Diameter 0.11 in [2.79 mm]

TNC Male to TNC Male Cable Using
RG188 Coax with HeatShrink



PE3434/HS

Connectors

Description	Connector 1	Connector 2
Type	TNC Male	TNC Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 µin minimum	100 µin minimum

Environmental Specifications

Operating Range Temperature -55 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

TNC Male to TNC Male Cable Using RG188 Coax with HeatShrink



PE3434/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3434/HS - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3434/HS-12 = 12 inches long cable
PE3434/HS-100cm = 100 cm long cable


TNC Male to TNC Male Cable Using RG188 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to TNC Male Cable Using RG188 Coax with HeatShrink PE3434/HS](#)

URL: <https://www.pasternack.com/tnc-male-to-tnc-male-cable-using-rg188-with-heatshrink-pe3434-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3434/HS CAD Drawing
TNC Male to TNC Male Cable Using RG188 Coax with HeatShrink



- NOTES:
- 1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - 3. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE MILLIMETERS.		PE PASTERNAK an INFINITE® brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES:		Website: www.Pasternack.com		SCALE	
X = ±.2 [5]		Phone: 1.866.727.8376 1.949.261.1920		NONE	
.XX = ±.02 [0.5]				SHEET	
.XXX = ±.005 [0.13]				1 OF 1	
FRACTIONS ± 1/32					
ANGLES ± 1°					
CABLE LENGTH TOLERANCES:		DESCRIPTION			
>12 [305] ≤ 60 [1524] = ±.125 [-.0]		TNC MALE TO TNC MALE CABLE USING RG188 COAX WITH HEATSHRINK			
>60 [1524] ≤ 120 [3048] = ±.125 [-.0]					
>120 [3048] ≤ 300 [7620] = ±.125 [-.0]					
>300 [7620] = ±.125 [-.0]					
ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS OF INDIVIDUAL COMPONENTS MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.					
		ITEM NO.		REV	
		A		A	
		CAGE CODE		DRAWN BY	
		53919		HBAKKE	
		PE3434/HS			