

TNC Female Bulkhead to SMA Male Right Angle Cable
36 Inch Length Using RG188 Coax with HeatShrink



RF Cable Assemblies Technical Data Sheet

PE34345/HS-36

Configuration

- Connector 1: TNC Female Bulkhead
- Connector 2: SMA Male Right Angle
- Cable Type: RG188
- Coax Flex Type: Flexible

Features

- Max Frequency 1 GHz
- PTFE Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE34345/HS-36 TNC female bulkhead to SMA male right angle 36 inch cable using RG188 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to SMA cable assembly has a female to male gender configuration with 50 ohm flexible RG188 coax. The PE34345/HS-36 TNC female to SMA male cable assembly operates to 1 GHz. The right angle SMA interface on the RG188 cable allows for easier connections in tight spaces. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.5:1	
Operating Voltage (AC)			2,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz

Insertion Loss (Typ.)

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Female Bulkhead to SMA Male Right Angle Cable 36 Inch Length Using RG188 Coax with HeatShrink PE34345/HS-36](#)

TNC Female Bulkhead to SMA Male Right Angle Cable 36 Inch Length Using RG188 Coax with HeatShrink



RF Cable Assemblies Technical Data Sheet

PE34345/HS-36

Mechanical Specifications

Cable Assembly

Length*	36 in [914.4 mm]
Weight	0.095 lbs [43.09 g]

Cable

Cable Type	RG188
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	PTFE, White
Jacket Diameter	0.11 in [2.79 mm]

Connectors

Description	Connector 1	Connector 2
Type	TNC Female Bulkhead Threaded	SMA Male Right Angle Threaded
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in minimum	50 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	100 μ in minimum
Coupling Nut Material and Plating		Brass, Nickel
Coupling Nut Plating Specification		100 μ in minimum
Hex Size		5/16 inch
Torque		3 in-lbs [0.34 Nm]

Environmental Specifications
Temperature

Operating Range -55 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Female Bulkhead to SMA Male Right Angle Cable 36 Inch Length Using RG188 Coax with HeatShrink PE34345/HS-36](#)

TNC Female Bulkhead to SMA Male Right Angle Cable
36 Inch Length Using RG188 Coax with HeatShrink




RF Cable Assemblies Technical Data Sheet

PE34345/HS-36

How to Order

Part Number Configuration:



Example: PE34345/HS-12 = 12 inches long cable
PE34345/HS-100cm = 100 cm long cable

TNC Female Bulkhead to SMA Male Right Angle Cable 36 Inch Length Using RG188 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Female Bulkhead to SMA Male Right Angle Cable 36 Inch Length Using RG188 Coax with HeatShrink PE34345/HS-36](#)

URL: <https://www.pasternack.com/tnc-female-bulkhead-to-sma-male-cable-36-inch-length-using-rg188-with-heatshrink-pe34345-hs-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE34345/HS-36 CAD Drawing

TNC Female Bulkhead to SMA Male Right Angle Cable 36 Inch
Length Using RG188 Coax with HeatShrink

