

## SMA Male to SMC Plug Cable 36 Inch Length Using PE-B100 Coax




### PE34460LF-36

#### Configuration

- Connector 1: SMA Male
- Connector 2: SMC Plug
- Cable Type: PE-B100
- Coax Flex Type: Flexible

#### Features

- Max Frequency 6 GHz
- 62% Phase Velocity
- Double Shielded
- PVC Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE34460LF-36 SMA male to SMC plug 36 inch cable using PE-B100 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMC cable assembly has a male to plug gender configuration with 50 ohm flexible PE-B100 coax. The PE34460LF-36 SMA male to SMC plug cable assembly operates to 6 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		62		%
Capacitance		38 [124.67]		pF/ft [pF/m]
Operating Voltage (AC)			335	V <sub>rms</sub>

#### Mechanical Specifications

##### Cable Assembly

Width/Diameter	0.312 in [7.92 mm]
Weight	0.012 lbs [5.44 g]

## SMA Male to SMC Plug Cable 36 Inch Length Using PE-B100 Coax



### PE34460LF-36

#### Cable

Cable Type	PE-B100
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	PVC
Shield Layer 2	Tinned Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.101 in [2.57 mm]

#### Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMC Plug
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification	30μ in. Minimum	30μ in. minimum
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100μ in. Minimum	100μ in. minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100μ in. Minimum	
Hex Size	5/16 in	1/4 in
Torque	5 in-lbs 0.57 Nm	

#### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:  
Values at 25°C, sea level.

## SMA Male to SMC Plug Cable 36 Inch Length Using PE-B100 Coax




### PE34460LF-36

#### Typical Performance Data

#### How to Order

Part Number Configuration:



Example: PE34460LF-12 = 12 inches long cable  
PE34460LF-100cm = 100 cm long cable

SMA Male to SMC Plug Cable 36 Inch Length Using PE-B100 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMC Plug Cable 36 Inch Length Using PE-B100 Coax PE34460LF-36](https://www.pasternack.com/sma-male-smc-plug-pe-b100-cable-assembly-pe34460lf-36-p.aspx)

URL: <https://www.pasternack.com/sma-male-smc-plug-pe-b100-cable-assembly-pe34460lf-36-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

