

SMA Male to SMC Plug Cable 72 Inch Length Using PE-B100 Coax




PE34460LF-72

Configuration

- Connector 1: SMA Male
- Connector 2: SMC Plug
- Cable Type: PE-B100
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- 62% Phase Velocity
- Double Shielded
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE34460LF-72 SMA male to SMC plug 72 inch cable using PE-B100 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMC cable assembly has a male to plug gender configuration with 50 ohm flexible PE-B100 coax. The PE34460LF-72 SMA male to SMC plug cable assembly operates to 6 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------|-------------|---------|---------|--------------|
| Frequency Range | DC | | 6 | GHz |
| VSWR | | | 1.4:1 | |
| Velocity of Propagation | 62 | | | % |
| Capacitance | 38 [124.67] | | | pF/ft [pF/m] |
| Operating Voltage (AC) | | | 335 | Vrms |

Mechanical Specifications

Cable Assembly

Width/Diameter 0.312 in [7.92 mm]
Weight 0.012 lbs [5.44 g]

SMA Male to SMC Plug Cable 72 Inch Length Using PE-B100 Coax



PE34460LF-72

Cable

| | |
|--------------------------------------|---------------------|
| Cable Type | PE-B100 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Stranded |
| Inner Conductor Material and Plating | Copper Clad Steel |
| Dielectric Type | PE |
| Number of Shields | 2 |
| Shield Layer 1 | PVC |
| Shield Layer 2 | Tinned Copper Braid |
| Jacket Material | PVC, Black |
| Jacket Diameter | 0.101 in [2.57 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|------------------------------------|-----------------------|------------------------|
| Type | SMA Male | SMC Plug |
| Specification | MIL-STD-348A | MIL-STD-348A |
| Impedance | 50 Ohms | 50 Ohms |
| Configuration | Straight | Straight |
| Contact Material and Plating | Brass, Gold | Beryllium Copper, Gold |
| Contact Plating Specification | 30 μ in. Minimum | 30 μ in. minimum |
| Dielectric Type | PTFE | Teflon |
| Body Material and Plating | Brass, Nickel | Brass, Nickel |
| Body Plating Specification | 100 μ in. Minimum | 100 μ in. minimum |
| Coupling Nut Material and Plating | Brass, Nickel | |
| Coupling Nut Plating Specification | 100 μ in. Minimum | |
| Hex Size | 5/16 in | 1/4 in |
| Torque | 5 in-lbs 0.57 Nm | |

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

SMA Male to SMC Plug Cable 72 Inch Length Using PE-B100 Coax




PE34460LF-72

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE34460LF-12 = 12 inches long cable
PE34460LF-100cm = 100 cm long cable

SMA Male to SMC Plug Cable 72 Inch Length Using PE-B100 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMC Plug Cable 72 Inch Length Using PE-B100 Coax PE34460LF-72](#)

URL: <https://www.pasternack.com/sma-male-smc-plug-pe-b100-cable-assembly-pe34460lf-72-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE34460LF-72 CAD Drawing

SMA Male to SMC Plug Cable 72 Inch Length Using PE-B100 Coax

