



# N Male to N Male Right Angle Low Loss Test Cable 100 CM Length Using PE-P142LL Coax, RoHS

## TECHNICAL DATA SHEET

PE345-100CM

The PE340's high performance test cable's 0.195 inch diameter and 83% phase velocity offer very low loss performance up to 18 GHz. The durable stainless steel connectors and FEP jacket provide a cost effective design ideal for test environments where a rugged cable assembly is required. The series is offered with Type N, TNC, and SMA connectors all rated to 18 GHz. A heavy Duty boot provides improved strain relief and adds to the durability of the cable assemblies. These cable assemblies are built using a double shielded flexible cable, providing excellent shielding effectiveness of greater than 95 dB. All PE340 cable assemblies are 100% Continuity, Hi-POT, and RF tested to published specifications. Custom lengths are built to order and shipped same day.

- 83% Velocity of Propagation
- Shielding effectiveness > 95 dB
- Maximum VSWR is < 1.35:1 to 18 GHz
- Minimum Bend Radius of 1.5 inches
- Operating Temperature range of -55 to +125 °C
- · ROHS and REACH Compliant
- · Same day shipment of custom lengths
- · 100% Continuity, Hi-Pot, and RF tested

#### Configuration

Connector 1 N Male

Connector 2 N Male Right Angle
Cable Type PE-P142LL

**Electrical Specifications** 

Frequency Range, GHz
Impedance, Ohms
50
Maximum VSWR
1.35:1
Velocity of Propagation, %
RF Shielding, dB
95

#### Typical Performance by Frequency

Frequency 1

Frequency, MHz 400

Insertion Loss 0.045 dB [0.15 dB]

Power Handling, KWatts 1.2

Frequency 2

Frequency, MHz 1000

Insertion Loss 0.072 dB [0.24 dB]

Power Handling, Watts 700

Frequency 3

Frequency, GHz

Insertion Loss 0.103 dB [0.34 dB]

Power Handling, Watts 500

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Right Angle Low Loss Test Cable 100 CM Length Using PE-P142LL Coax, RoHS PE345-100CM





# N Male to N Male Right Angle Low Loss Test Cable 100 CM Length Using PE-P142LL Coax, RoHS

## **TECHNICAL DATA SHEET**

PE345-100CM

Frequency 4

Frequency, GHz

Insertion Loss 0.127 dB [0.42 dB]

Power Handling, Watts 400

Frequency 5

Frequency, GHz

0.166 dB [0.54 dB] Insertion Loss 300

Power Handling, Watts

Frequency 6 Frequency, GHz

10 0.24 dB [0.79 dB] Insertion Loss

Power Handling, Watts 220

Frequency 7 Frequency, GHz

18 Insertion Loss 0.33 dB [1.08 dB]

Power Handling, Watts 160

**Electrical Specification Notes:** Power handling values are calculated based on Cable properties. Power handling will vary based on the actual

VSWR of the cable assembly.

**Mechanical Specifications** 

Cable

Cable Type PE-P142LL

No of Shields Dielectric Type **PTFE** Jacket Material **FEP** Cable Color Green

Jacket Diameter, in [mm] 0.195 [4.95]

**Connector 1** 

Type N Male

Configuration Straight

Inner Conductor Material and Plating Beryllium Copper, Gold Inner Conductor Plating Specification ASTM-B488, 50µ Inch. Outer Conductor Material and Plating Passivated Stainless Steel

Outer Conductor Plating Specification SAE-AMS-2700

Coupling Nut Material and Plating Passivated Stainless Steel

Coupling Nut Plating Specification SAE-AMS-2700

Hex Size, Inch 3/4 14 [1.58] Torque, in-lbs [Nm] Dielectric Type **PTFE** 

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Right Angle Low Loss Test Cable 100 CM Length Using PE-P142LL Coax, **RoHS PE345-100CM** 





# N Male to N Male Right Angle Low Loss Test Cable 100 CM Length Using PE-P142LL Coax, RoHS

## **TECHNICAL DATA SHEET**

PE345-100CM

**Connector 2** 

Type N Male Right Angle Configuration Right Angle

Inner Conductor Material and Plating
Inner Conductor Plating Specification
Outer Conductor Material and Plating
Passivated Stainless Steel

Outer Conductor Plating Specification SAE-AMS-2701

Coupling Nut Material and Plating Passivated Stainless Steel

Coupling Nut Plating Specification SAE-AMS-2701

 Hex Size, Inch
 3/4

 Torque, in-lbs [Nm]
 14 [1.58]

Body Material and Plating Passivated Stainless Steel

Body Plating Specification SAE-AMS-2701

Dielectric Type PTFE

**Temperature** 

Temperature Operating Range, deg C -55 to +125

Size

 Length, in [cm]
 39.37 [100]

 Diameter, in [mm]
 1.14 [28.96]

 Weight, lbs [g]
 0.154 [69.85]

 Repeated Minimum Bend Radius, in [mm]
 1 [25.4]

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes

REACH Compliant 07/19/2006

**Plotted and Other Data** 

Notes: Values at 25 °C, sea level

N Male to N Male Right Angle Low Loss Test Cable 100 CM Length Using PE-P142LL Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Right Angle Low Loss Test Cable 100 CM Length Using PE-P142LL Coax, RoHS PE345-100CM

URL: http://www.pasternack.com/n-male-n-male-pe-p142ll-cable-assembly-pe345-100cm-p.aspx

PE345-100CM CAD Drawing

N Male to N Male Right Angle Low Loss Test Cable 100 CM
Length Using PE-P142LL Coax, RoHS

