



N Male to N Male Right Angle Low Loss Test Cable 12 Inch Length Using PE-P142LL Coax, RoHS

TECHNICAL DATA SHEET

PE345-12

The PE340's high performance test cable's 0.195 inch diameter and 83% phase velocity offer very low loss performance up to 18 GHz. The durable stainless steel connectors and FEP jacket provide a cost effective design ideal for test environments where a rugged cable assembly is required. The series is offered with Type N, TNC, and SMA connectors all rated to 18 GHz. A heavy Duty boot provides improved strain relief and adds to the durability of the cable assemblies. These cable assemblies are built using a double shielded flexible cable, providing excellent shielding effectiveness of greater than 95 dB. All PE340 cable assemblies are 100% Continuity, Hi-POT, and RF tested to published specifications. Custom lengths are built to order and shipped same day.

- 83% Velocity of Propagation
- Shielding effectiveness > 95 dB
- Maximum VSWR is < 1.35:1 to 18 GHz
- Minimum Bend Radius of 1.5 inches
- Operating Temperature range of -55 to +125 °C
- · ROHS and REACH Compliant
- · Same day shipment of custom lengths
- 100% Continuity, Hi-Pot, and RF tested

Configuration

Connector 1 N Male
Connector 2 N Male Right Angle
Cable Type PE-P142LL

Electrical Specifications

Typical Performance by Frequency

Frequency 1

Frequency, MHz 400

Insertion Loss 0.045 dB [0.15 dB]

Power Handling, KWatts 1.2

Frequency 2

Frequency, MHz 1000

Insertion Loss 0.072 dB [0.24 dB]

Power Handling, Watts 700

Frequency 3

Frequency, GHz

Insertion Loss 0.103 dB [0.34 dB]

Power Handling, Watts 500

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Right Angle Low Loss Test Cable 12 Inch Length Using PE-P142LL Coax, RoHS PE345-12

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com





N Male to N Male Right Angle Low Loss Test Cable 12 Inch Length Using PE-P142LL Coax, RoHS

TECHNICAL DATA SHEET

PE345-12

Frequency 4

Frequency, GHz

Insertion Loss Power Handling, Watts

Frequency 5

Frequency, GHz

Insertion Loss

Power Handling, Watts

Frequency 6

Frequency, GHz

Insertion Loss

Power Handling, Watts

Frequency 7

Frequency, GHz

Insertion Loss

Power Handling, Watts

Electrical Specification Notes:

0.127 dB [0.42 dB]

400

0.166 dB [0.54 dB]

300

10

0.24 dB [0.79 dB]

220

18

0.33 dB [1.08 dB]

160

Power handling values are calculated based on Cable properties. Power handling will vary based on the actual

VSWR of the cable assembly.

Mechanical Specifications

Cable

Cable Type

No of Shields

Dielectric Type Jacket Material

Cable Color

Jacket Diameter, in [mm]

PE-P142LL

PTFE

FEP

Green

0.195 [4.95]

Connector 1

Type N Male

Configuration Straight

Inner Conductor Material and Plating Beryllium Copper, Gold Inner Conductor Plating Specification ASTM-B488, 50µ Inch. Outer Conductor Material and Plating Passivated Stainless Steel

Outer Conductor Plating Specification SAE-AMS-2700

Coupling Nut Material and Plating Passivated Stainless Steel

Coupling Nut Plating Specification SAE-AMS-2700

Hex Size, Inch 3/4

Torque, in-lbs [Nm] 14 [1.58] Dielectric Type **PTFE**

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Right Angle Low Loss Test Cable 12 Inch Length Using PE-P142LL Coax, RoHS PE345-12

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com





N Male to N Male Right Angle Low Loss Test Cable 12 Inch Length Using PE-P142LL Coax, RoHS

TECHNICAL DATA SHEET

PE345-12

Connector 2

Type N Male Right Angle Configuration Right Angle

Inner Conductor Material and Plating Beryllium Copper, Gold Inner Conductor Plating Specification ASTM-B488, 50µ In. Minimum

Outer Conductor Material and Plating Passivated Stainless Steel
Outer Conductor Plating Specification SAE-AMS-2701

Coupling Nut Material and Plating Passivated Stainless Steel

Coupling Nut Plating Specification SAE-AMS-2701

 Hex Size, Inch
 3/4

 Torque, in-lbs [Nm]
 14 [1.58]

Body Material and Plating Passivated Stainless Steel

Body Plating Specification SAE-AMS-2701

Dielectric Type PTFE

Temperature

Temperature Operating Range, deg C -55 to +125

Size

 Length, in [mm]
 12 [304.8]

 Diameter, in [mm]
 1.14 [28.96]

 Weight, lbs [g]
 0.063 [28.58]

 Repeated Minimum Bend Radius, in [mm]
 1 [25.4]

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes

REACH Compliant 07/19/2006

Plotted and Other Data

Notes: Values at 25 °C, sea level

N Male to N Male Right Angle Low Loss Test Cable 12 Inch Length Using PE-P142LL Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male to N Male Right Angle Low Loss Test Cable 12 Inch Length Using PE-P142LL Coax, RoHS PE345-12

URL: http://www.pasternack.com/n-male-n-male-pe-p142ll-cable-assembly-pe345-12-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623

Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE345-12 CAD DrawingN Male to N Male Right Angle Low Loss Test Cable 12 Inch Length Using PE-P142LL Coax, RoHS

