


SMA Female Bulkhead to MMCX Plug Right Angle Cable 60 Inch Length Using RG316 Coax

PE34686-60




Configuration

- Connector 1: SMA Female Bulkhead
- Connector 2: MMCX Plug Right Angle
- Cable Type: RG316
- Coax Flex Type: Flexible

Features

- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE34686-60 SMA female bulkhead to MMCX plug right angle 60 inch cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to MMCX cable assembly has a female to plug gender configuration with 50 ohm flexible RG316 coax. The right angle MMCX interface on the RG316 cable allows for easier connections in tight spaces. Our RF cable assembly with SMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		32 [104.99]		pF/ft [pF/m]

Mechanical Specifications


Cable Assembly

Width/Diameter	0.312 in [7.92 mm]
Weight	0.026 lbs [11.79 g]

Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver

SMA Female Bulkhead to MMCX Plug Right Angle Cable 60 Inch Length Using RG316 Coax



PE34686-60

Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.098 in [2.49 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Female Bulkhead	MMCX Plug Right Angle
Specification		BS EN 122340
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Gold	Brass, Gold
Contact Plating Specification		30μ in. minimum
Dielectric Type		Teflon
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification		3μ in. minimum

Environmental Specifications

Operating Range Temperature	-55 to +155 deg C
-----------------------------	-------------------


Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

SMA Female Bulkhead to MMCX Plug Right Angle Cable 60 Inch Length Using RG316 Coax

PE34686-60



Typical Performance Data

How to Order

Part Number Configuration:

PE34686

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length
Base Number

Example: PE34686-12 = 12 inches long cable
PE34686-100cm = 100 cm long cable

SMA Female Bulkhead to MMCX Plug Right Angle Cable 60 Inch Length Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female Bulkhead to MMCX Plug Right Angle Cable 60 Inch Length Using RG316 Coax PE34686-60](https://www.pasternack.com/sma-female-mmcx-plug-rg316u-cable-assembly-pe34686-60-p.aspx)

URL: <https://www.pasternack.com/sma-female-mmcx-plug-rg316u-cable-assembly-pe34686-60-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE34686-60 CAD Drawing

SMA Female Bulkhead to MMCX Plug Right Angle Cable 60 Inch Length Using RG316 Coax

