



Reverse Polarity SMA Female Bulkhead to MMCX Plug  
Right Angle Cable 24 Inch Length Using RG316 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet



PE34728LF-24

**Configuration**

- Connector 1: SMA Female Reverse Polarity Bulkhead
- Connector 2: MMCX Plug Right Angle
- Cable Type: RG316

**Features**

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



**Applications**

- General Purpose
- Laboratory Use

**Description**

Pasternack's PE34728LF-24 reverse polarity SMA female bulkhead to MMCX plug right angle 24 inch cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity SMA to MMCX cable assembly has a female to plug gender configuration with 50 ohm flexible RG316 coax. The PE34728LF-24 reverse polarity SMA female to MMCX plug cable assembly operates to 3 GHz. The right angle MMCX interface on the RG316 cable allows for easier connections in tight spaces. Our RF cable assembly with SMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Operating Voltage (AC)			250	Vrms
Jacket Spark			2,000	Vrms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Female Bulkhead to MMCX Plug Right Angle Cable 24 Inch Length Using RG316 Coax , LF Solder PE34728LF-24](#)



# Reverse Polarity SMA Female Bulkhead to MMCX Plug Right Angle Cable 24 Inch Length Using RG316 Coax , LF Solder

## RF Cable Assemblies Technical Data Sheet

PE34728LF-24

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	3	GHz
Insertion Loss (Max.)	0.62	0.776	1.059	1.359	1.459	dB

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.3dB of connector loss.

### Mechanical Specifications

#### Cable Assembly

Length*	24 in [609.6 mm]
Diameter	0.315 in [8 mm]

#### Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.098 in [2.49 mm]

### Connectors

Description	Connector 1	Connector 2
Type	SMA Female Reverse Polarity Bulkhead	MMCX Plug Right Angle
Specification		BS EN 122340
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	50 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification	100 µin minimum	3 µin minimum

#### Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm 3/8"$ , whichever is greater.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Female Bulkhead to MMCX Plug Right Angle Cable 24 Inch Length Using RG316 Coax , LF Solder PE34728LF-24](#)



Reverse Polarity SMA Female Bulkhead to MMCX Plug  
Right Angle Cable 24 Inch Length Using RG316 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE34728LF-24

**Environmental Specifications**

**Temperature**

Operating Range


-55 to +155 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

**Typical Performance Data**



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Female Bulkhead to MMCX Plug Right Angle Cable 24 Inch Length Using RG316 Coax , LF Solder PE34728LF-24](#)



Reverse Polarity SMA Female Bulkhead to MMCX Plug  
Right Angle Cable 24 Inch Length Using RG316 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE34728LF-24

**How to Order**

Part Number Configuration:

**PE34728LF - xx uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE34728LF-12 = 12 inches long cable  
PE34728LF-100cm = 100 cm long cable

Reverse Polarity SMA Female Bulkhead to MMCX Plug Right Angle Cable 24 Inch Length Using RG316 Coax , LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Female Bulkhead to MMCX Plug Right Angle Cable 24 Inch Length Using RG316 Coax , LF Solder PE34728LF-24](https://www.pasternack.com/sma-female-mmcx-plug-rg316u-cable-assembly-pe34728lf-24-p.aspx)

URL: <https://www.pasternack.com/sma-female-mmcx-plug-rg316u-cable-assembly-pe34728lf-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE34728LF-24 CAD Drawing

Reverse Polarity SMA Female Bulkhead to MMCX Plug Right Angle  
Cable 24 Inch Length Using RG316 Coax , LF Solder



NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE  
PE34728LF

**PASTERNAK**  
THE ENGINEER'S RF SOURCE  
Pasternack Enterprises, Inc.  
P.O. Box 16759 | Irvine | CA | 92623  
Phone: (949) 261-1920 | Fax: (949) 261-7451  
Website: www.pasternack.com | E-Mail: sales@pasternack.com

CAD FILE 09/29/18

CAGE CODE 53919

SCALE N/A

SIZE A

CN2245