

## N Male to MCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink In 200 CM Length



### RF Cable Assemblies Technical Data Sheet



PE35276/HS-200CM

#### Configuration

- Connector 1: N Male
- Connector 2: MCX Plug Right Angle
- Cable Type: RG316-DS

#### Features

- Max Frequency 3 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE35276/HS-200CM type N male to MCX plug right angle 200 cm cable using RG316-DS coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to MCX cable assembly has a male to plug gender configuration with 50 ohm flexible RG316-DS coax. The PE35276/HS-200CM type N male to MCX plug cable assembly operates to 3 GHz. The right angle MCX interface on the RG316-DS cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to MCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink In 200 CM Length PE35276/HS-200CM](#)

## N Male to MCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink In 200 CM Length



### RF Cable Assemblies Technical Data Sheet

**PE35276/HS-200CM**

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.5:1	
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.61	0.94	1.42	2.11	3.86	dB

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of  $0.1 * \text{SQRT}(F \text{GHz})$  dB per connector.

#### Mechanical Specifications

##### Cable Assembly

Length\* 78.74 in [200 cm]

Weight 0.174 lbs [78.93 g]

##### Cable

Cable Type RG316-DS  
 Impedance 50 Ohms  
 Inner Conductor Type Stranded  
 Inner Conductor Material and Plating Copper Clad Steel, Silver PTFE  
 Dielectric Type PTFE  
 Number of Shields 2  
 Shield Layer 1 Silver Plated Copper Braid  
 Shield Layer 2 Silver Plated Copper Braid  
 Jacket Material FEP, Tan  
 Jacket Diameter 0.114 in [2.9 mm]

One Time Minimum Bend Radius 0.59 in [14.99 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to MCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink In 200 CM Length PE35276/HS-200CM](#)

## N Male to MCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink In 200 CM Length



### RF Cable Assemblies Technical Data Sheet

PE35276/HS-200CM

#### Connectors

Description	Connector 1	Connector 2
Type	N Male	MCX Plug Right Angle
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	
Contact Plating Specification	30µ in. minimum	
Dielectric Type	Teflon	
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100µ in. minimum	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100µ in. minimum	

#### Environmental Specifications

##### Temperature

Operating Range

-65 to +165 deg C

#### Compliance Certifications (see product page for current document)

#### Plotted and Other Data

##### Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to MCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink In 200 CM Length PE35276/HS-200CM](#)

N Male to MCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink In 200 CM Length




RF Cable Assemblies Technical Data Sheet

PE35276/HS-200CM

**How to Order**

Part Number Configuration:



Example: PE35276/HS-12 = 12 inches long cable  
PE35276/HS-100cm = 100 cm long cable

N Male to MCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink In 200 CM Length from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to MCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink In 200 CM Length PE35276/HS-200CM](#)

URL: <https://www.pasternack.com/A-male-to-mcx-plug-cable-200-cm-leAgth-usiAg-rg316-ds-with-heatshriAk-pe35276-hs-200cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

**PE35276/HS-200CM CAD Drawing**  
 N Male to MCX Plug Right Angle Cable Using RG316-  
 DS Coax with HeatShrink In 200 CM Length

