



Reverse Polarity SMA Jack Bulkhead to Reverse Polarity SMA Plug Cable Using RG316 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet


PE35474/HS

Configuration

- Connector 1: SMA Jack Reverse Polarity Bulkhead
- Connector 2: SMA Plug Reverse Polarity
- Cable Type: RG316
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE35474/HS reverse polarity SMA jack bulkhead to reverse polarity SMA plug cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity SMA to reverse polarity SMA cable assembly has a jack to plug gender configuration with 50 ohm flexible RG316 coax. The PE35474/HS reverse polarity SMA jack to reverse polarity SMA plug cable assembly operates to 3 GHz. Our RF cable assembly with SMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Jack Bulkhead to Reverse Polarity SMA Plug Cable Using RG316 Coax with HeatShrink PE35474/HS](#)



Reverse Polarity SMA Jack Bulkhead to Reverse Polarity SMA Plug Cable Using RG316 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE35474/HS

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Jacket Spark			2,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.11	0.16	0.238	0.38	0.58	dB/ft
	0.36	0.52	0.78	1.25	1.9	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.033 lbs [14.97 g]

Cable

Cable Type RG316
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper Clad Steel, Silver
 Dielectric Type PTFE
 Number of Shields 1
 Shield Layer 1 Silver Plated Copper Braid
 Jacket Material FEP, Tan
 Jacket Diameter 0.102 in [2.59 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Jack Bulkhead to Reverse Polarity SMA Plug Cable Using RG316 Coax with HeatShrink PE35474/HS](#)



Reverse Polarity SMA Jack Bulkhead to Reverse Polarity
SMA Plug Cable Using RG316 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE35474/HS

Connectors

Description	Connector 1	Connector 2
Type	SMA Jack Reverse Polarity Bulkhead	SMA Plug Reverse Polarity
Specification		MIL-STD-348
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Gold
Contact Plating Specification	50 µin minimum	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	QQ-N-290
Coupling Nut Material and Plating		Brass, Nickel
Coupling Nut Plating Specification		QQ-N-290
Hex Size		5/16 inch
Torque		3 in-lbs [0.34 Nm]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Jack Bulkhead to Reverse Polarity SMA Plug Cable Using RG316 Coax with HeatShrink PE35474/HS](#)



Reverse Polarity SMA Jack Bulkhead to Reverse Polarity SMA Plug Cable Using RG316 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE35474/HS

How to Order

Part Number Configuration:

PE35474/HS

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE35474/HS-12 = 12 inches long cable
PE35474/HS-100cm = 100 cm long cable

Reverse Polarity SMA Jack Bulkhead to Reverse Polarity SMA Plug Cable Using RG316 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity SMA Jack Bulkhead to Reverse Polarity SMA Plug Cable Using RG316 Coax with HeatShrink PE35474/HS](#)

URL: <https://www.pasternack.com/reverse-polarity-sma-jack-bulkhead-to-reverse-polarity-sma-plug-cable-using-rg316-with-heatshrink-pe35474-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE35474/HS CAD Drawing

Reverse Polarity SMA Jack Bulkhead to Reverse Polarity SMA Plug Cable Using RG316 Coax with HeatShrink

