

MCX Jack to MCX Plug Right Angle Cable Using RG316 Coax with HeatShrink, LF Solder




RF Cable Assemblies Technical Data Sheet

PE35585LF/HS


Configuration

- Connector 1: MCX Jack
- Connector 2: MCX Plug Right Angle
- Cable Type: RG316



Features

- 69% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE35585LF/HS MCX jack to MCX plug right angle cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MCX to MCX cable assembly has a jack to plug gender configuration with 50 ohm flexible RG316 coax. The right angle MCX interface on the RG316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69		%
Jacket Spark			2,000	Vrms

Mechanical Specifications

Cable Assembly

Weight 0.023 lbs [10.43 g]

Cable

Cable Type RG316

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Jack to MCX Plug Right Angle Cable Using RG316 Coax with HeatShrink, LF Solder PE35585LF/HS](#)

MCX Jack to MCX Plug Right Angle Cable Using RG316 Coax with HeatShrink, LF Solder



RF Cable Assemblies Technical Data Sheet

PE35585LF/HS

Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.102 in [2.59 mm]

Connectors

Description	Connector 1	Connector 2
Type	MCX Jack	MCX Plug Right Angle
Specification	MIL-C-39012	CECC 22220
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Gold	Brass, Gold
Contact Plating Specification	MIL-G-45204	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	QQ-N-290	100 μ in minimum

Environmental Specifications

Temperature

Operating Range

-40 to +60 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Jack to MCX Plug Right Angle Cable Using RG316 Coax with HeatShrink, LF Solder PE35585LF/HS](#)

MCX Jack to MCX Plug Right Angle Cable Using
RG316 Coax with HeatShrink, LF Solder




RF Cable Assemblies Technical Data Sheet

PE35585LF/HS

How to Order

Part Number Configuration:



Example: PE35585LF/HS-12 = 12 inches long cable
PE35585LF/HS-100cm = 100 cm long cable

MCX Jack to MCX Plug Right Angle Cable Using RG316 Coax with HeatShrink, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Jack to MCX Plug Right Angle Cable Using RG316 Coax with HeatShrink, LF Solder PE35585LF/HS](#)

URL: <https://www.pasternack.com/mcx-jack-to-mcx-plug-cable-using-rg316-with-heatshrink-lf-solder-pe35585lf-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE35585LF/HS CAD Drawing

MCX Jack to MCX Plug Right Angle Cable Using RG316 Coax with HeatShrink, LF Solder

