



N Male Right Angle to N Female Cable Using RG8 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE35758/HS

Configuration

- Connector 1: N Male Right Angle
- Connector 2: N Female
- Cable Type: RG8

Features

- 66% Phase Velocity
- PVC (NC) Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE35758/HS type N male right angle to type N female cable using RG8 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to type N cable assembly has a male to female gender configuration with 50 ohm flexible RG8 coax. The right angle type N interface on the RG8 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Weight	0.338 lbs [153.31 g]
--------	----------------------

Cable

Cable Type	RG8
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to N Female Cable Using RG8 Coax with HeatShrink PE35758/HS](#)



N Male Right Angle to N Female Cable
Using RG8 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE35758/HS

Jacket Material PVC (NC), Black
Jacket Diameter 0.405 in [10.29 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male Right Angle	N Female
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Brass, Gold	
Contact Plating Specification	30 μ in minimum	
Dielectric Type	PTFE	
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	
Coupling Nut Material and Plating	Brass, Nickel	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to N Female Cable Using RG8 Coax with HeatShrink PE35758/HS](#)




N Male Right Angle to N Female Cable Using RG8 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE35758/HS

How to Order

Part Number Configuration:



Example: PE35758/HS-12 = 12 inches long cable
PE35758/HS-100cm = 100 cm long cable

N Male Right Angle to N Female Cable Using RG8 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to N Female Cable Using RG8 Coax with HeatShrink PE35758/HS](#)

URL: <https://www.pasternack.com/n-male-right-angle-to-n-female-cable-using-rg8-with-heatshrink-pe35758-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE35758/HS CAD Drawing

N Male Right Angle to N Female Cable Using RG8 Coax with HeatShrink

