

## N Male to N Male Cable Using RG393 Coax with Double HeatShrink, LF Solder

### RF Cable Assemblies Technical Data Sheet

**PE3607LF/HS2**

#### Configuration

- Connector 1: N Male
- Connector 2: N Male
- Cable Type: RG393

#### Features

- Max Frequency 10 GHz
- 69.5% Phase Velocity
- Double Shielded
- FEP Jacket

#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3607LF/HS2 type N male to type N male cable using RG393 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to type N cable assembly has a male to male gender configuration with 50 ohm flexible RG393 coax. The PE3607LF/HS2 type N male to type N male cable assembly operates to 10 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Cable Using RG393 Coax with Double HeatShrink, LF Solder PE3607LF/HS2](#)

## N Male to N Male Cable Using RG393 Coax with Double HeatShrink, LF Solder

### RF Cable Assemblies Technical Data Sheet

**PE3607LF/HS2**

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	GHz
VSWR			1.4:1	
Velocity of Propagation	69.5			%
Group Delay	□		□	
Capacitance	29.4 [96.46]			pF/ft [pF/m]
Inductance	□		□	
DC Resistance Inner Conductor	□		□	
DC Resistance Outer Conductor	□		□	
Operating Voltage (AC)				

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	5	10	GHz
Insertion Loss (Typ.)						

Electrical Specification Notes:

#### Mechanical Specifications

##### Cable Assembly

Length*	[]
Weight	lbs [0 g]

##### Cable

Cable Type	RG393
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.39 in [9.91 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Cable Using RG393 Coax with Double HeatShrink, LF Solder PE3607LF/HS2](#)

## N Male to N Male Cable Using RG393 Coax with Double HeatShrink, LF Solder

### RF Cable Assemblies Technical Data Sheet

**PE3607LF/HS2**

#### Connectors

Description	Connector 1	Connector 2
Type	N Male	N Male
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 $\mu$ in minimum	30 $\mu$ in minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		
Outer Conductor Plating Specification		
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 $\mu$ in minimum	100 $\mu$ in minimum

#### Environmental Specifications

##### Temperature

Operating Range

-55 to +165 deg C

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Cable Using RG393 Coax with Double HeatShrink, LF Solder PE3607LF/HS2](#)

N Male to N Male Cable Using RG393 Coax  
with Double HeatShrink, LF Solder

**RF Cable Assemblies Technical Data Sheet**

**PE3607LF/HS2**

**How to Order**

Part Number Configuration:

**PE3607LF/HS2**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3607LF/HS2-12 = 12 inches long cable  
PE3607LF/HS2-100cm = 100 cm long cable

N Male to N Male Cable Using RG393 Coax with Double HeatShrink, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Cable Using RG393 Coax with Double HeatShrink, LF Solder PE3607LF/HS2](#)

URL: <https://www.pasternack.com/n-male-n-male-rg393u-cable-assembly-pe3607lf-hs2-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.