

MCX Plug Right Angle to MMCX Plug Right Angle Cable Using RG178 Coax with HeatShrink, LF Solder




PE36384LF/HS

Configuration

- Connector 1: MCX Plug Right Angle
- Connector 2: MMCX Plug Right Angle
- Cable Type: RG178
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE36384LF/HS MCX plug right angle to MMCX plug right angle cable using RG178 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MCX to MMCX cable assembly has a plug to plug gender configuration with 50 ohm flexible RG178 coax. The PE36384LF/HS MCX plug to MMCX plug cable assembly operates to 3 GHz. The right angle MCX and right angle MMCX interfaces on the RG178 cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]
Operating Voltage (AC)			170	Vrms

Specifications by Frequency

MCX Plug Right Angle to MMCX Plug Right Angle Cable Using RG178 Coax with HeatShrink, LF Solder



PE36384LF/HS

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency		100	250	500	1000	
PE36384LF/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.14	0.21	0.24	0.44	0.784	dB/ft	
			0.46	0.69	0.78	1.46	2.58	dB/m	
PE36384LF/HS-6	6 inch	Insertion Loss (Typ.)	0.47	0.51	0.52	0.63	0.8	dB	0.017
PE36384LF/HS-9	9 inch	Insertion Loss (Typ.)	0.51	0.56	0.58	0.74	0.99	dB	0.018
PE36384LF/HS-12	12 inch	Insertion Loss (Typ.)	0.54	0.61	0.64	0.85	1.19	dB	0.019
PE36384LF/HS-24	24 inch	Insertion Loss (Typ.)	0.68	0.82	0.88	1.29	1.97	dB	0.025
PE36384LF/HS-36	36 inch	Insertion Loss (Typ.)	0.82	1.03	1.11	1.74	2.76	dB	0.03

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.2 dB
Loss due to Connector 2:	0.2 dB
Base Weight:	0.019 pounds
Additional Weight per Inch:	0.00075 pounds

Mechanical Specifications

Cable Assembly

Weight 0.019 lbs [8.62 g]

Cable

Cable Type	RG178
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.072 in [1.83 mm]
Repeated Minimum Bend Radius	0.4 in [10.16 mm]

Connectors

Description	Connector 1	Connector 2
Type	MCX Plug Right Angle	MMCX Plug Right Angle
Specification	CECC 22220	BS EN 122340
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification	100 µin minimum	3 µin minimum

MCX Plug Right Angle to MMCX Plug Right Angle Cable Using RG178 Coax with HeatShrink, LF Solder



PE36384LF/HS

Environmental Specifications

Operating Range Temperature -40 to +60 deg C

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE36384LF/HS-12 = 12 inches long cable
PE36384LF/HS-100cm = 100 cm long cable

MCX Plug Right Angle to MMCX Plug Right Angle Cable Using RG178 Coax with HeatShrink, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MCX Plug Right Angle to MMCX Plug Right Angle Cable Using RG178 Coax with HeatShrink, LF Solder PE36384LF/HS](#)

URL: <https://www.pasternack.com/mcx-plug-right-angle-to-mmcx-plug-cable-using-rg178-with-heatshrink-lf-solder-pe36384lf-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE36384LF/HS CAD Drawing

MCX Plug Right Angle to MMCX Plug Right Angle Cable Using RG178 Coax with HeatShrink, LF Solder

