

## Reverse Polarity TNC Plug to Reverse Polarity TNC Plug Cable Using RG316 Coax with HeatShrink





### PE36780/HS

#### Configuration

- Connector 1: TNC Plug Reverse Polarity
- Connector 2: TNC Plug Reverse Polarity
- Cable Type: RG316
- Coax Flex Type: Flexible

#### Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE36780/HS reverse polarity TNC plug to reverse polarity TNC plug cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity TNC to reverse polarity TNC cable assembly has a plug to plug gender configuration with 50 ohm flexible RG316 coax. The PE36780/HS reverse polarity TNC plug to reverse polarity TNC plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]
Operating Voltage (AC)			500	Vrms
Jacket Spark			2,000	Vrms

#### Specifications by Frequency

## Reverse Polarity TNC Plug to Reverse Polarity TNC Plug Cable Using RG316 Coax with HeatShrink



### PE36780/HS

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	3000	MHz	
PE36780/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.11	0.16	0.24	0.38	0.58	dB/ft	
			0.37	0.53	0.79	1.25	1.91	dB/m	
PE36780/HS-12	12 inch	Insertion Loss (Typ.)	0.31	0.36	0.44	0.58	0.78	dB	0.084
PE36780/HS-24	24 inch	Insertion Loss (Typ.)	0.42	0.52	0.68	0.96	1.36	dB	0.095
PE36780/HS-36	36 inch	Insertion Loss (Typ.)	0.53	0.68	0.92	1.34	1.94	dB	0.105
PE36780/HS-48	48 inch	Insertion Loss (Typ.)	0.64	0.84	1.16	1.72	2.52	dB	0.115
PE36780/HS-72	72 inch	Insertion Loss (Typ.)	0.86	1.16	1.63	2.48	3.68	dB	0.135

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB

Loss due to Connector 2: 0.1 dB

Base Weight: 0.084 pounds

Additional Weight per Inch: 0.00084 pounds

### Mechanical Specifications

#### Cable Assembly

Weight 0.084 lbs [38.1 g]

#### Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.102 in [2.59 mm]

## Reverse Polarity TNC Plug to Reverse Polarity TNC Plug Cable Using RG316 Coax with HeatShrink



### PE36780/HS

#### Connectors

Description	Connector 1	Connector 2
Type	TNC Plug Reverse Polarity	TNC Plug Reverse Polarity
Specification	MIL-C-39012	MIL-C-39012
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 $\mu$ in minimum	30 $\mu$ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	200 $\mu$ in minimum	200 $\mu$ in minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	200 $\mu$ in minimum	200 $\mu$ in minimum

#### Environmental Specifications

Operating Range Temperature -55 to +165 deg C

#### Compliance Certifications

(see product page for current document)

#### Plotted and Other Data

Notes:

## Reverse Polarity TNC Plug to Reverse Polarity TNC Plug Cable Using RG316 Coax with HeatShrink




### PE36780/HS

#### Typical Performance Data

#### How to Order

Part Number Configuration:



Example: PE36780/HS-12 = 12 inches long cable  
PE36780/HS-100cm = 100 cm long cable

Reverse Polarity TNC Plug to Reverse Polarity TNC Plug Cable Using RG316 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to Reverse Polarity TNC Plug Cable Using RG316 Coax with HeatShrink PE36780/HS](#)

URL: <https://www.pasternack.com/reverse-polarity-tnc-plug-to-reverse-polarity-tnc-plug-cable-using-rg316-with-heatshrink-pe36780-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE36780/HS CAD Drawing

Reverse Polarity TNC Plug to Reverse Polarity TNC Plug Cable Using RG316 Coax with HeatShrink

