



SMA Male to SMA Male Test Cable 60 Inch  
Length Using PE-P102 Coax, RoHS

TECHNICAL DATA SHEET

PE370-60

**Configuration**

Connector 1	SMA Male
Connector 2	SMA Male
Cable Type	PE-P102

**Electrical Specifications**

Frequency Range	DC to 26.5 GHz
Impedance	50 Ohms
Maximum VSWR	1.4:1
Velocity of Propagation	76 %
RF Shielding	90 dB
Peak Power	550 Watts

**Typical Performance by Frequency**

**Frequency 1**

Frequency	6 GHz
VSWR	1.25:1
Insertion Loss,	3.8 dB
Power Handling, Watts	160

**Frequency 2**

Frequency	12 GHz
VSWR	1.25:1
Insertion Loss	5.4 dB
Power Handling	110 Watts

**Frequency 3**

Frequency	18 GHz
VSWR	1.25:1
Insertion Loss	6.8 dB
Power Handling	89 Watts

**Frequency 4**

Frequency	26.5 GHz
VSWR	1.4:1
Insertion Loss	8.35 dB
Power Handling	73 Watts

**Mechanical Specifications**

**Temperature**

Temperature Operating Range	-65 to +165 deg C
-----------------------------	-------------------

**Size**

Length	60 in [152.4 cm]
Diameter	0.35 in [8.89 mm]
Cable Color	Gray

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Male Test Cable 60 Inch Length Using PE-P102 Coax, RoHS PE370-60



SMA Male to SMA Male Test Cable 60 Inch  
Length Using PE-P102 Coax, RoHS

TECHNICAL DATA SHEET

PE370-60

One Time Minimum Bend Radius	0.32 in [8.13 mm]
Repeated Minimum Bend Radius	0.32 in [8.13 mm]

**Cable**

Cable Type	PE-P102
Inner Conductor Type	Stranded
Cable Inner Conductor	Copper, Silver
No of Shields	3
Dielectric Type	PTFE
Jacket Material	ETFE
Jacket Diameter	0.102 in [2.59 mm]

**Connector 1**

Type	SMA Male
Configuration	Straight
Inner Conductor Material and Plating	Beryllium Copper, Gold
Inner Conductor Plating Specification	ASTM-B488 50µ In. Minimum
Coupling Nut Material and Plating	Passivated Stainless Steel
Coupling Nut Plating Specification	SAE-AMS-2700
Hex Size	5/16 Inch
Torque	8 in-lbs [0.9 Nm]
Body Material and Plating	Passivated Stainless Steel
Body Plating Specification	SAE-AMS-2700
Dielectric Type	PTFE

**Connector 2**

Type	SMA Male
Configuration	Straight
Inner Conductor Material and Plating	Beryllium Copper, Gold
Inner Conductor Plating Specification	ASTM-B488 50µ In. Minimum
Coupling Nut Material and Plating	Passivated Stainless Steel
Coupling Nut Plating Specification	SAE-AMS-2700
Hex Size	5/16 Inch
Torque	8 in-lbs [0.9 Nm]
Body Material and Plating	Passivated Stainless Steel
Body Plating Specification	SAE-AMS-2700
Dielectric Type	PTFE

**Compliance Certifications** (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

RoHS Compliant	Yes
----------------	-----

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Test Cable 60 Inch Length Using PE-P102 Coax, RoHS PE370-60](#)



SMA Male to SMA Male Test Cable 60 Inch  
Length Using PE-P102 Coax, RoHS

TECHNICAL DATA SHEET

PE370-60

Notes:

- Values at +25 °C, sea level

SMA Male to SMA Male Test Cable 60 Inch Length Using PE-P102 Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Test Cable 60 Inch Length Using PE-P102 Coax, RoHS PE370-60](#)

URL: <http://www.pasternack.com/sma-male-sma-male-pe-p102-cable-assembly-pe370-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE370-60 CAD Drawing

SMA Male to SMA Male Test Cable 60 Inch Length Using PE-P102 Coax, RoHS



NOTE:  
LABEL FOR CABLE LENGTHS 48" OR SHORTER TO BE CENTERED. 48" OR LONGER WILL BE 12" AWAY FROM CONNECTOR.

How To Order		Part # Ext.	Length In Inches	Part # Ext.	Length In Centimeters
Part Number Configuration PE3 [zzz] - [xx] [uu]  00 - 99999  CM = Centimeters < Blank > = Inches Length	Examples PE3000-100 PE3000-100CM	-12	12"	-25CM	25Cm
		-24	24"	-50CM	50Cm
		-36	36"	-75CM	75Cm
		-48	48"	-100CM	100Cm
		-60	60"	-125CM	125Cm
		-xx	Custom Length	-xxCM	Custom Length

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].  
4. LENGTH TOLERANCE IS  $\pm 1.5\%$  OR  $3/8"$ , WHICHEVER IS GREATER.

DWG TITLE  
**PE370**

**PE PASTERNAK®**  
Pasternack Enterprises, Inc.  
P.O. Box 16759 | Irvine | CA | 92623  
Phone: (949) 261-1920 | Fax: (949) 261-7451  
Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO. 53919

CAD FILE 091713

SCALE N/A

SIZE A

2233