



N Male to N Male Right Angle Cable 36 Inch Length Using 1/2 inch Helical Coax, RoHS

TECHNICAL DATA SHEET

PE37970-36

N Male to N Male Right Angle Cable 36 Inch Length Using 1/2 inch Helical Coax, RoHS

Configuration

Connector 1	N Male
Connector 2	N Male Right Angle
Cable Type	1/2" Helical

Electrical Specifications

Frequency Range, GHz	DC to 2.7
Impedance, Ohms	50
Maximum VSWR	1.14:1
Passive Intermodulation, dBc	-156

Typical Performance by Frequency

Frequency 1

Frequency, MHz	1000
VSWR	1.06:1
Insertion Loss	0.022 dB/ft + 0.02 dB [0.07 dB/m + 0.02 dB]

Frequency 2

Frequency, GHz	2.2
VSWR	1.08:1
Insertion Loss	0.034 dB/ft + 0.02 [0.11 dB/m + 0.02 dB]

Frequency 3

Frequency, GHz	2.7
VSWR	1.09:1
Insertion Loss	0.038 dB/ft + 0.02 dB [0.12 dB/m + 0.02 dB]

Mechanical Specifications

Cable Assembly

Cable Type	1/2" Helical
------------	--------------

Temperature

Temperature Operating Range, deg C	-55 to +85
------------------------------------	------------

Size

Length, in [mm]	36 [914.4]
One Time Minimum Bend Radius, in [mm]	2.75 [69.85]
Repeated Minimum Bend Radius, in [mm]	4.9 [124.46]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Right Angle Cable 36 Inch Length Using 1/2 inch Helical Coax, RoHS PE37970-36](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



N Male to N Male Right Angle Cable 36 Inch Length Using 1/2 inch Helical Coax, RoHS

TECHNICAL DATA SHEET

PE37970-36

Cable

Center Conductor Type	Solid
Cable Inner Conductor	Copper Clad Aluminum
No of Shields	1
Dielectric Type	PE (F)
Jacket Material	PE
Jacket Diameter, in [mm]	0.54 [13.72]

Connector 1

Type	N Male
Configuration	Straight
Inner Conductor Material and Plating	Brass, Silver
Outer Conductor Material and Plating	Brass, Silver
Coupling Nut Material and Plating	Brass, Nickel
Hex Size, mm	19
Body Material and Plating	Brass, Silver
Dielectric Type	PTFE

Connector 2

Type	N Male Right Angle
Configuration	Right Angle
Inner Conductor Material and Plating	Brass, Silver
Outer Conductor Material and Plating	Brass, Silver
Coupling Nut Material and Plating	Brass, Nickel
Hex Size, mm	19
Body Material and Plating	Brass, Silver
Dielectric Type	PTFE

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant	Yes
----------------	-----

Plotted and Other Data

Notes:	Values at 25 °C, sea level
--------	----------------------------

N Male to N Male Right Angle Cable 36 Inch Length Using 1/2 inch Helical Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Right Angle Cable 36 Inch Length Using 1/2 inch Helical Coax, RoHS PE37970-36](http://www.pasternack.com/n-male-n-male-1-2-inch-helical-cable-assembly-pe37970-36)

URL: <http://www.pasternack.com/n-male-n-male-1-2-inch-helical-cable-assembly-pe37970-36-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE37970-36 CAD Drawing

N Male to N Male Right Angle Cable 36 Inch Length Using 1/2 inch Helical Coax, RoHS



How To Order		Part # Ext.	Length In Inches	Part # Ext.	Length In Centimeters
Part Number Configuration PE3 [ZZ] [YY] - [XX] [UU] 00 - 99999 LF = RoHS Compliant < Blank > = Standard Note: LF applies only to RF cables	Examples PE3000LF-100 PE3000-100 PE3000LF-100CM PE3000-100CM	-12	12"	-25CM	25Cm
		-24	24"	-50CM	50Cm
		-36	36"	-75CM	75Cm
		-48	48"	-100CM	100Cm
		-60	60"	-125CM	125Cm
		-XX	Custom Length	-XXCM	Custom Length

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].
 4. LENGTH TOLERANCE IS ± 1.5% OR 3/8", WHICHEVER IS GREATER.

DWG TITLE
PE37970

FSCM NO. 53919

CAD FILE 111407

SCALE N/A

SIZE A

2233

PE PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
 Phone: (949) 261-1920 | Fax: (949) 261-7451
 Website: www.pasternack.com | E-Mail: sales@pasternack.com