



N Male Right Angle to HN Male Cable Using RG214 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE37584/HS

Configuration

- Connector 1: N Male Right Angle
- Connector 2: HN Male
- Cable Type: RG214

Features

- Max Frequency 3 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE37584/HS type N male right angle to HN male cable using RG214 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to HN cable assembly has a male to male gender configuration with 50 ohm flexible RG214 coax. The PE37584/HS type N male to HN male cable assembly operates to 3 GHz. The right angle type N interface on the RG214 cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to HN Male Cable Using RG214 Coax with HeatShrink PE37584/HS](#)



N Male Right Angle to HN Male Cable Using RG214 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE37584/HS

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Operating Voltage (AC)			1,500	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.02	0.029	0.044	0.076	0.141	dB/ft
	0.07	0.1	0.14	0.25	0.46	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the HN male connector 0.2 dB for the N male connector.

Mechanical Specifications

Cable Assembly

Weight 0.367 lbs [166.47 g]

Cable

Cable Type RG214
 Impedance 50 Ohms
 Inner Conductor Type Stranded
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PE
 Number of Shields 2
 Shield Layer 1 Silver Plated Copper Braid
 Shield Layer 2 Silver Plated Copper Braid
 Jacket Material PVC, Black
 Jacket Diameter 0.425 in [10.8 mm]
 Repeated Minimum Bend Radius 1.6 in [40.64 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to HN Male Cable Using RG214 Coax with HeatShrink PE37584/HS](#)



N Male Right Angle to HN Male Cable Using
RG214 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE37584/HS

Connectors

Description	Connector 1	Connector 2
Type	N Male Right Angle	HN Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification		100 µin minimum

Environmental Specifications

Temperature

Operating Range

-20 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to HN Male Cable Using RG214 Coax with HeatShrink PE37584/HS](#)



N Male Right Angle to HN Male Cable Using RG214 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE37584/HS

How to Order

Part Number Configuration:

PE37584/HS

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE37584/HS-12 = 12 inches long cable
PE37584/HS-100cm = 100 cm long cable

N Male Right Angle to HN Male Cable Using RG214 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male Right Angle to HN Male Cable Using RG214 Coax with HeatShrink PE37584/HS](#)

URL: <https://www.pasternack.com/n-male-right-angle-to-hn-male-cable-using-rg214-with-heatshrink-pe37584-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE37584/HS CAD Drawing

N Male Right Angle to HN Male Cable Using RG214 Coax with HeatShrink

