



75 Ohm BNC Male to 75 Ohm MCX Plug Cable
Using 75 Ohm RG179 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE38533LF

Configuration

- Connector 1: BNC Male
- Connector 2: MCX Plug
- Cable Type: RG179

Features

- Max Frequency 1 GHz
- 70% Phase Velocity
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE38533LF 75 ohm BNC male to 75 ohm MCX plug cable using 75 ohm RG179 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack BNC to MCX cable assembly has a male to plug gender configuration with 75 ohm flexible RG179 coax. The PE38533LF BNC male to MCX plug cable assembly operates to 1 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm BNC Male to 75 Ohm MCX Plug Cable Using 75 Ohm RG179 Coax , LF Solder PE38533LF](#)



75 Ohm BNC Male to 75 Ohm MCX Plug Cable
Using 75 Ohm RG179 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE38533LF

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		70		%
Capacitance		19.4 [63.65]		pF/ft [pF/m]
Operating Voltage (AC)			250	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Typ.)	0.074	0.126	0.155	0.203	0.3	dB/ft
	0.24	0.41	0.51	0.67	0.98	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.046 lbs [20.87 g]

Cable

Cable Type	RG179
Impedance	75 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.1 in [2.54 mm]
Repeated Minimum Bend Radius	0.4 in [10.16 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm BNC Male to 75 Ohm MCX Plug Cable Using 75 Ohm RG179 Coax , LF Solder PE38533LF](#)



75 Ohm BNC Male to 75 Ohm MCX Plug Cable
Using 75 Ohm RG179 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE38533LF

Connectors

Description	Connector 1	Connector 2
Type	BNC Male	MCX Plug
Impedance	75 Ohms	75 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification	100 µin minimum	3 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 µin minimum	

Environmental Specifications

Temperature

Operating Range -55 to +155 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm BNC Male to 75 Ohm MCX Plug Cable Using 75 Ohm RG179 Coax , LF Solder PE38533LF](#)



75 Ohm BNC Male to 75 Ohm MCX Plug Cable
Using 75 Ohm RG179 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE38533LF

How to Order

Part Number Configuration:

PE38533LF

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE38533LF-12 = 12 inches long cable
PE38533LF-100cm = 100 cm long cable

75 Ohm BNC Male to 75 Ohm MCX Plug Cable Using 75 Ohm RG179 Coax , LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm BNC Male to 75 Ohm MCX Plug Cable Using 75 Ohm RG179 Coax , LF Solder PE38533LF](#)

URL: <https://www.pasternack.com/75-ohm-bnc-male-to-75-ohm-mcx-plug-cable-using-rg179-lf-solder-pe38533lf-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE38533LF CAD Drawing

75 Ohm BNC Male to 75 Ohm MCX Plug Cable Using 75 Ohm RG179 Coax , LF Solder

