

## SMA Male to SMA Female Bulkhead Cable 48 Inch Length Using RG316 Coax



## **RF Cable Assemblies - PE3835-48**

### Configuration

· Connector 1: SMA Male

• Connector 2: SMA Female Bulkhead

· Cable Type: RG316

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Capacitance		32 [104.99]		pF/ft [pF/m]

#### **Mechanical Specifications**

**Cable Assembly** 

 Length
 48 in [121.92 cm]

 Diameter
 0.312 in [7.92 mm]

 Weight
 0.025 lbs [11.34 g]

 Cable Color
 Tan

 Connection Type
 In-Series

Cable

Cable Type RG316
Impedance 50 Ohms
Inner Conductor Type Stranded
Imper Conductor Material and Plating Conner Conne

Inner Conductor Material and Plating Copper Clad Steel, Silver Dielectric Type PTFE

Number of Shields 1
Shield Layer 1 Silver Plated Copper Braid
Jacket Material FEP

Jacket Diameter 0.098 in [2.49 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Bulkhead Cable 48 Inch Length Using RG316 Coax PE3835-48

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



# SMA Male to SMA Female Bulkhead Cable 48 Inch Length Using RG316 Coax



## **RF Cable Assemblies - PE3835-48**

#### Connectors

Description	Connector 1	Connector 2	
Туре	SMA Male	SMA Female Bulkhead	
Specification	MIL-STD-348A		
Impedance	50 Ohms	50 Ohms	
Connection Method	Standard	Standard	
Contact Material and Plating	Brass, Gold	Gold	
Contact Plating Specification	30μ in. Minimum		
Dielectric Type	PTFE		
Coupling Nut Material and Plating	Brass, Nickel		
Coupling Nut Plating Specification	100μ in. Minimum		
Hex Size	5/16 in		
Torque	5 in-lbs [0.57 Nm]	[]	
Body Material and Plating	Brass, Nickel	Brass, Nickel	
Body Plating Specification	100μ in. Minimum		

#### **Environmental Specifications**

Compliance Certifications (visit www.Pasternack.com for current document)

For RoHS Compliant version, use PE3835LF-48. Contact Pasternack if product cannot be found. REACH Compliant 06/18/2012

#### **Plotted and Other Data**

Notes:

· Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Bulkhead Cable 48 Inch Length Using RG316 Coax PE3835-48



## SMA Male to SMA Female Bulkhead Cable 48 Inch Length Using RG316 Coax



### **RF Cable Assemblies - PE3835-48**

#### **How to Order**

Part Number Configuration:

PE3835 - xx uu

Unit of Measure:
cm = Centimeters
<br/>
<br/>
<br/>
Chlank> = Inches
Length
Base Number

Example: PE3835-12 = 12 inches long cable PE3835-100cm = 100 cm long cable

SMA Male to SMA Female Bulkhead Cable 48 Inch Length Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Bulkhead Cable 48 Inch Length Using RG316 Coax PE3835-48

URL: http://www.pasternack.com/sma-male-sma-female-rg316u-cable-assembly-pe3835-48-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

