

## 7/16 DIN Male Right Angle to C Male Right Angle Cable Using RG393 Coax, LF Solder




### PE38548/LF

#### Configuration

- Connector 1: 7/16 DIN Male Right Angle
- Connector 2: C Male Right Angle
- Cable Type: RG393
- Coax Flex Type: Flexible

#### Features

- Double Shielded
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE38548/LF 7/16 DIN male right angle to type C male right angle cable using RG393 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 7/16 DIN to type C cable assembly has a male to male gender configuration with 50 ohm flexible RG393 coax. The right angle 7/16 DIN and right angle type C interfaces on the RG393 cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		32 [104.99]		pF/ft [pF/m]

#### Mechanical Specifications

##### Cable Assembly

Weight 0.641 lbs [290.75 g]

##### Cable

Cable Type RG393  
 Impedance 50 Ohms  
 Inner Conductor Type Stranded  
 Inner Conductor Material and Plating Copper, Silver  
 Dielectric Type PTFE  
 Number of Shields 2

## 7/16 DIN Male Right Angle to C Male Right Angle Cable Using RG393 Coax, LF Solder



### PE38548/LF

Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.39 in [9.91 mm]

### Connectors

Description	Connector 1	Connector 2
Type	7/16 DIN Male Right Angle	C Male Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Silver	Silver
Contact Plating Specification	QQ-S-365	QQ-S-365
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	QQ-N-290	QQ-N-290
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	QQ-N-290	QQ-N-290
Hex Size	1 1/4 in	
Torque	18 in-lbs 2.03 Nm	

### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:  
Values at 25°C, sea level.

## 7/16 DIN Male Right Angle to C Male Right Angle Cable Using RG393 Coax, LF Solder



### PE38548/LF

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**PE38548/LF - xx uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches

Length

Base Number

Example: PE38548/LF-12 = 12 inches long cable  
PE38548/LF-100cm = 100 cm long cable

7/16 DIN Male Right Angle to C Male Right Angle Cable Using RG393 Coax, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [7/16 DIN Male Right Angle to C Male Right Angle Cable Using RG393 Coax, LF Solder PE38548/LF](#)

URL: <https://www.pasternack.com/7-16-din-male-right-angle-to-c-male-cable-using-rg393-lf-solder-pe38548-lf-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE38548/LF CAD Drawing
7/16 DIN Male Right Angle to C Male Right Angle Cable Using RG393 Coax, LF Solder

