

Waterproof IP68 SMA Male (Plug) to N Male (Plug) Low Loss Cable Using LMR-240 Coax




PE3C0044/WP

Configuration

- Connector 1: SMA Male
- Connector 2: N Male
- Cable Type: LMR-240
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket
- Silicone Connector Boot
- IP68 Rated



Applications

- General Purpose
- Laboratory Use

Description

The Pasternack PE3C0044/WP is a weatherproof low loss cable assembly that comes with SMA male connection with weatherproof boot on one end and type N male on the other. Pasternack's RF coaxial cable assembly products are designed for typical use, production, laboratory test and measurement, defense/military, aerial antenna towers, etc. The low loss cable has a 50 Ohm impedance and is specifically ready for quicker shipment than most in the industry can provide.

This weatherproof low loss RF cable assembly operates at a maximum frequency of 6 GHz. Our RF cable assembly has a PE jacket with 0.240 inches diameter. The SMA male to type N male cable assembly PE3C0044/WP is built with LMR-240 coax, which has a flexible design. This RF cable assembly with 0.5 inches diameter has copper as cable's inner conducting material and PE (F) dielectric type. The weatherproof boot low loss cable can operate at a temperature range of -40 to 85 degrees C. Additional dimensions, specifications, and CAD drawings for this PE3C0044/WP low loss RF cable are available on our downloadable PDF datasheet.

Pasternack stocks a wide selection of weatherproof low loss cable assemblies that ship the same business day as ordered from our warehouse. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal SMA male to type N male cable assembly as per your requirements.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------------|---------|-------------|---------|-----------------------|
| Frequency Range | DC | | 6 | GHz |
| VSWR | | | 1.4:1 | |
| Velocity of Propagation | | 84 | | % |
| RF Shielding | 90 | | | dB |
| Capacitance | | 24.2 [79.4] | | pF/ft [pF/m] |
| Inductance | | 0.06 [0.2] | | uH/ft [uH/m] |
| DC Resistance Inner Conductor | | 3.2 [10.5] | | Ohms/1000ft [Ohms/Km] |

Waterproof IP68 SMA Male (Plug) to N Male (Plug) Low Loss Cable Using LMR-240 Coax



PE3C0044/WP

Electrical Specifications

| Description | Minimum | Typical | | | | | Maximum | Units |
|--------------------------------------|--------------|---------|--|--|--|-----------------------|---------|-------|
| DC Resistance Outer Conductor | 3.89 [12.76] | | | | | Ohms/1000ft [Ohms/Km] | | |
| Dielectric Withstanding Voltage (DC) | | | | | | 1,500 | | |
| Jacket Spark | | | | | | 5,000 | | |

Specifications by Frequency

| Part Number | Length | Description | F1 | F2 | F3 | F4 | F5 | Units | Weight (lbs) |
|----------------|--------------------------|-----------------------|-------|-------|-------|-------|-------|-------|--------------|
| | | Frequency | 250 | 500 | 1000 | 2500 | 6000 | MHz | |
| PE3C0044/WP | Custom Lengths Available | Insertion Loss (Typ.) | 0.039 | 0.055 | 0.079 | 0.129 | 0.204 | dB/ft | |
| | | | 0.13 | 0.19 | 0.26 | 0.43 | 0.67 | dB/m | |
| PE3C0044/WP-24 | 24 Inch | Insertion Loss (Typ.) | 0.28 | 0.31 | 0.36 | 0.46 | 0.61 | dB | 0.647 |
| PE3C0044/WP-36 | 36 Inch | Insertion Loss (Typ.) | 0.32 | 0.37 | 0.44 | 0.59 | 0.82 | dB | 0.68 |
| PE3C0044/WP-48 | 48 Inch | Insertion Loss (Typ.) | 0.36 | 0.42 | 0.52 | 0.72 | 1.02 | dB | 0.713 |
| PE3C0044/WP-60 | 60 Inch | Insertion Loss (Typ.) | 0.4 | 0.48 | 0.6 | 0.85 | 1.22 | dB | 0.746 |

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

| | |
|-----------------------------|----------------|
| Loss due to Connector 1: | 0.1 dB |
| Loss due to Connector 2: | 0.1 dB |
| Base Weight: | 0.614 pounds |
| Additional Weight per Inch: | 0.00275 pounds |

Mechanical Specifications

Cable Assembly

| | |
|----------------|----------------------|
| Width/Diameter | 0.5 in [12.7 mm] |
| Weight | 0.614 lbs [278.51 g] |

Cable

| | |
|--------------------------------------|------------------------|
| Cable Type | LMR-240 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper |
| Dielectric Type | PE (F) |
| Number of Shields | 2 |
| Shield Layer 1 | Aluminum Tape |
| Shield Layer 2 | Tinned Copper Braid |
| Jacket Material | PE |
| Jacket Diameter | 0.24 in [6.1 mm] |
| One Time Minimum Bend Radius | 0.75 in [19.05 mm] |
| Repeated Minimum Bend Radius | 2.5 in [63.5 mm] |
| Bending Moment | 0.25 lbs-ft [0.34 N-m] |
| Flat Plate Crush | 20 lbs/in [0.36 Kg/mm] |
| Tensile Strength | 80 lbs [36.29 Kg] |

Waterproof IP68 SMA Male (Plug) to N Male (Plug) Low Loss Cable Using LMR-240 Coax



PE3C0044/WP

Connectors

| Description | Connector 1 | Connector 2 |
|------------------------------------|-------------------|----------------------|
| Type | SMA Male | N Male |
| Option | Weatherproof Boot | |
| Specification | | MIL-STD-348A |
| Impedance | 50 Ohms | 50 Ohms |
| Configuration | Straight | Straight |
| Contact Material and Plating | Brass, Gold | Brass, Gold |
| Contact Plating Specification | | 30 μ in minimum |
| Dielectric Type | PTFE | PTFE |
| Body Material and Plating | Brass, Gold | Brass, Nickel |
| Body Plating Specification | | 100 μ in minimum |
| Coupling Nut Material and Plating | Brass, Gold | Brass, Nickel |
| Coupling Nut Plating Specification | | 100 μ in minimum |
| Boot Material | Silicone | Silicone |

Environmental Specifications

| | |
|--------------------------------|------------------|
| Operating Range Temperature | -40 to +85 deg C |
| Ingress Protection (IP) Rating | IP68 |

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

Waterproof IP68 SMA Male (Plug) to N Male (Plug) Low Loss Cable Using LMR-240 Coax




PE3C0044/WP

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C0044/WP-12 = 12 inches long cable
PE3C0044/WP-100cm = 100 cm long cable

Waterproof IP68 SMA Male (Plug) to N Male (Plug) Low Loss Cable Using LMR-240 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Waterproof IP68 SMA Male \(Plug\) to N Male \(Plug\) Low Loss Cable Using LMR-240 Coax PE3C0044/WP](#)

URL: <https://www.pasternack.com/waterproof-ip68-sma-male-plug-to-n-male-plug-low-loss-cable-using-lmr-240-pe3c0044-wp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C0044/WP CAD Drawing

Waterproof IP68 SMA Male (Plug) to N Male (Plug) Low Loss Cable Using LMR-240 Coax

