



SMA Male to SMA Male Cable 24 Inch Length Using LMR-240 Coax

TECHNICAL DATA SHEET

PE3C0052-24

SMA Male to SMA Male Cable 24 Inch Length Using LMR-240 Coax

Configuration

Connector 1	SMA Male
Connector 2	SMA Male
Cable Type	LMR-240
Impedance, Ohms	50

Mechanical Specifications

Cable Assembly

Cable Type	LMR-240
------------	---------

Temperature

Temperature Operating Range, deg C	-40 to +85
Temperature Storage Range, deg C	-70 to +85

Size

Length, in [mm]	24 [609.6]
Diameter, in [mm]	0.312 [7.92]
Weight, lbs [g]	0.026 [11.79]
Cable Color	Black
One Time Minimum Bend Radius, in [mm]	0.75 [19.05]
Repeated Minimum Bend Radius, in [mm]	2.5 [63.5]

Cable

No of Shields	2
Dielectric Type	PE (F)
Jacket Material	PE
Jacket Diameter, in [mm]	0.24 [6.1]

Connector 1

Type	SMA Male
Configuration	Straight
Inner Conductor Material and Plating	Phosphor Bronze, Gold
Coupling Nut Material and Plating	Brass, Gold
Hex Size, in	5/16
Torque, in-lbs [Nm]	5 [0.57]
Body Material and Plating	Brass, Gold
Dielectric Type	Teflon

Connector 2

Type	SMA Male
Configuration	Straight
Inner Conductor Material and Plating	Phosphor Bronze, Gold

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable 24 Inch Length Using LMR-240 Coax PE3C0052-24](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



SMA Male to SMA Male Cable 24 Inch
Length Using LMR-240 Coax

TECHNICAL DATA SHEET

PE3C0052-24

Coupling Nut Material and Plating
Hex Size, in
Torque, in-lbs [Nm]
Body Material and Plating
Dielectric Type

Brass, Gold
5/16
5 [0.57]
Brass, Gold
Teflon

Compliance Certifications (visit www.Pasternack.com for current document)

Plotted and Other Data

Notes:


Values at 25 °C, sea level

SMA Male to SMA Male Cable 24 Inch Length Using LMR-240 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMA Male Cable 24 Inch Length Using LMR-240 Coax PE3C0052-24](http://www.pasternack.com/sma-male-sma-male-lmr240-cable-assembly-pe3c0052-24)

URL: <http://www.pasternack.com/sma-male-sma-male-lmr240-cable-assembly-pe3c0052-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



How To Order			Part # Ext.	Length In Inches	Part # Ext.	Length In Centimeters
Part Number Configuration		Examples	-12	12"	-25CM	25Cm
PE3	zzz	yy	-xx	uu	-50CM	50Cm
00 - 99999	LF = RoHS Compliant < Blank > = Standard		-36	36"	-75CM	75Cm
			-48	48"	-100CM	100Cm
	Note: LF applies only to RF cables		-60	60"	-125CM	125Cm
			-xx	Custom Length	-xxCM	Custom Length



PASTERNAK®
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | **Fax:** (949) 261-7451
Website: www.pasternack.com | **E-Mail:** sales@pasternack.com

DWG TITLE

PE3C0052

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. LENGTH TOLERANCE IS ± 1.5% OR 3/8", WHICHEVER IS GREATER.

FSCM NO. 53919

CAD FILE 020513

SCALE N/A

SIZE A

2233