

75 Ohm TNC Male to 75 Ohm TNC Male Right Angle Cable Using 75 Ohm RG59 Coax




PE39254

Configuration

- Connector 1: TNC Male
- Connector 2: TNC Male Right Angle
- Cable Type: RG59
- Coax Flex Type: Flexible

Features

- 66% Phase Velocity
- PVC (NC) Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE39254 75 ohm TNC male to 75 ohm TNC male right angle cable using 75 ohm RG59 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to TNC cable assembly has a male to male gender configuration with 75 ohm flexible RG59 coax. The right angle TNC interface on the RG59 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		66		%
Capacitance		20.6 [67.59]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.139 lbs [63.05 g]

Cable

Cable Type	RG59
Impedance	75 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE

75 Ohm TNC Male to 75 Ohm TNC Male Right Angle Cable Using 75 Ohm RG59 Coax



PE39254

Number of Shields	1
Shield Layer 1	Copper Braid
Jacket Material	PVC (NC), Black
Jacket Diameter	0.242 in [6.15 mm]

Connectors

Description	Connector 1	Connector 2
Type	TNC Male	TNC Male Right Angle
Specification		MIL-STD-348
Impedance	75 Ohms	75 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Brass, Gold	Silver
Contact Plating Specification	30μ in. minimum	QQ-S-365
Dielectric Type		PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100μ in. minimum	QQ-N-290
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100μ in. minimum	QQ-N-290

Environmental Specifications

Operating Range Temperature	-25 to +70 deg C
-----------------------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

75 Ohm TNC Male to 75 Ohm TNC Male Right Angle Cable Using 75 Ohm RG59 Coax



PE39254

Typical Performance Data

How to Order

Part Number Configuration:

PE39254

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE39254-12 = 12 inches long cable
PE39254-100cm = 100 cm long cable

75 Ohm TNC Male to 75 Ohm TNC Male Right Angle Cable Using 75 Ohm RG59 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm TNC Male to 75 Ohm TNC Male Right Angle Cable Using 75 Ohm RG59 Coax PE39254](https://www.pasternack.com/75-ohm-tnc-male-to-75-ohm-tnc-male-right-angle-cable-using-75-ohm-rg59-coax-pe39254)

URL: <https://www.pasternack.com/75-ohm-tnc-male-to-75-ohm-tnc-male-cable-using-rg59-pe39254-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE39254 CAD Drawing
75 Ohm TNC Male to 75 Ohm TNC Male Right Angle Cable Using 75 Ohm RG59 Coax

