



N Male to N Male Right Angle Semi-Flexible Precision  
Cable Using PE-SR405FL Coax, RoHS

TECHNICAL DATA SHEET

PE39445

**Hand Formable N Male to N Male Right Angle Semi-Flexible Precision Cable Using PE-SR405FL Coax, RoHS**

Pasternack's formable cable assemblies are hand formable semi-rigid replacements that are an alternative to costly preformed assemblies. The formable semi-rigid cable alternatives are dimensionally and electrically similar to their semi-rigid counterpart and have a tinned-copper-braid outer shield that provides excellent RF shielding. The hand formable cable assemblies from Pasternack do not require special tooling to shape or reshape the assemblies and can replace standard semi-rigid versions. The assemblies are available with or without a PVC jacket and are RoHS compliant,

- Dimensionally and electrically the same as standard, solid outer conductor semi-rigid coax
- Cable may be formed by hand and does not require special tools to bend
- May be formed more than once without damaging the outer conductor
- High RF Shielding >100 dB
- 100% Hi-pot and continuity tested
- 100% VSWR tested to max frequency of assembly
- Standard and custom lengths ship the same day

**Configuration**

Connector 1	N Male
Connector 2	N Male Right Angle
Cable Type	PE-SR405FL

**Electrical Specifications**

Frequency Range, GHz	DC to 11
Impedance, Ohms	50
Maximum VSWR	1.5:1
Velocity of Propagation, %	69
RF Shielding, dB	100
Maximum Operating Voltage, Vrms	350

**Typical Performance by Frequency**

**Frequency 1**

Frequency, MHz	1000
Insertion Loss	0.225 dB/ft [ 0.74 dB/m ]

**Frequency 2**

Frequency, GHz	5
Insertion Loss	0.549 dB/ft [ 1.8 dB/m ]

**Frequency 3**

Frequency, GHz	10
Insertion Loss	0.812 dB/ft [ 2.66 dB/m ]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Right Angle Semi-Flexible Precision Cable Using PE-SR405FL Coax, RoHS PE39445](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



## N Male to N Male Right Angle Semi-Flexible Precision Cable Using PE-SR405FL Coax, RoHS

### TECHNICAL DATA SHEET

PE39445

#### Mechanical Specifications

##### Cable Assembly

Cable Type	PE-SR405FL
Diameter, in [mm]	0.086 [2.18]
Weight, lbs [g]	0.013 [5.9]
One Time Minimum Bend Radius, in [mm]	0.37 [9.4]

##### Cable

Center Conductor Type	Solid
Cable Inner Conductor	Copper Clad Steel, Silver
No of Shields	1
Dielectric Type	PTFE

##### Connector 1

Type	N Male
Configuration	Straight

##### Connector 2

Type	N Male Right Angle
Configuration	Right Angle

#### Compliance Certifications (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

RoHS Compliant	Yes
----------------	-----

#### Plotted and Other Data

Notes:	Values at 25 °C, sea level
--------	----------------------------

N Male to N Male Right Angle Semi-Flexible Precision Cable Using PE-SR405FL Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Right Angle Semi-Flexible Precision Cable Using PE-SR405FL Coax, RoHS PE39445](http://www.pasternack.com/n-male-n-male-pe-sr405fl-cable-assembly-pe39445-p.aspx)

URL: <http://www.pasternack.com/n-male-n-male-pe-sr405fl-cable-assembly-pe39445-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

# PE39445 CAD Drawing

N Male to N Male Right Angle Semi-Flexible Precision Cable Using PE-SR405FL Coax, RoHS



Note: This part is lead free.

Part Number Configuration		How To Order	
PE3	zzz yy - xx uu	Part # Ext.	Length In Inches
00 - 99999	LF = Lead Free < Blank > = Standard	-12	12"
Note: LF applies only to RF cables		-24	24"
		-36	36"
		-48	48"
		-60	60"
		-xx	Custom Length
		-25CM	25Cm
		-50CM	50Cm
		-75CM	75Cm
		-100CM	100Cm
		-125CM	125Cm
		-xxCM	Custom Length



**PASTERNAK ENTERPRISES, INC.**  
P.O. BOX 16759, IRVINE, CA 92623  
PHONE (949) 261-1920 FAX (949) 261-7451  
WEB ADDRESS: [www.pasternack.com](http://www.pasternack.com)  
E-MAIL ADDRESS: [sales@pasternack.com](mailto:sales@pasternack.com)  
**COAXIAL & FIBER OPTICS**

DWG TITLE  
**PE39445**

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES (mm).  
4. LENGTH TOLERANCE IS ± 1.5% OR 3/8", WHICHEVER IS GREATER.

REV. -	FSCM NO. 53919	CAD FILE 041912	SCALE N/A	SIZE A	2231
--------	----------------	-----------------	-----------	--------	------