

SMB Plug Right Angle to SMB Plug Right Angle Cable Using RG316-DS Coax with HeatShrink



PE3C0873/HS

Configuration

- Connector 1: SMB Plug Right Angle
- Connector 2: SMB Plug Right Angle
- Cable Type: RG316-DS
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- Shielding Effectivity > 85 dB
- 69.5% Phase Velocity
- Double Shielded
- FEP Jacket


Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C0873/HS SMB plug right angle to SMB plug right angle cable using RG316-DS coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMB to SMB cable assembly has a plug to plug gender configuration with 50 ohm flexible RG316-DS coax. The PE3C0873/HS SMB plug to SMB plug cable assembly operates to 3 GHz. The right angle SMB interfaces on the RG316-DS cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 85 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.



Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
RF Shielding	85			dB
Capacitance		28.96 [95.01]		pF/ft [pF/m]
DC Resistance Inner Conductor		83.82 [275]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		5.33 [17.49]		Ohms/1000ft [Ohms/Km]
Operating Voltage (AC)			250	Vrms

Specifications by Frequency

SMB Plug Right Angle to SMB Plug Right Angle Cable Using RG316-DS Coax with HeatShrink



PE3C0873/HS

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	3000	MHz	
PE3C0873/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.08	0.13	0.19	0.29	0.536	dB/ft	
			0.28	0.43	0.64	0.96	1.76	dB/m	
PE3C0873/HS-6	6 inch	Insertion Loss (Typ.)	0.45	0.47	0.5	0.55	0.67	dB	0.035
PE3C0873/HS-12	12 inch	Insertion Loss (Typ.)	0.49	0.53	0.6	0.69	0.94	dB	0.042
PE3C0873/HS-24	24 inch	Insertion Loss (Typ.)	0.57	0.66	0.79	0.98	1.48	dB	0.057
PE3C0873/HS-36	36 inch	Insertion Loss (Typ.)	0.65	0.79	0.99	1.27	2.01	dB	0.071
PE3C0873/HS-48	48 inch	Insertion Loss (Typ.)	0.74	0.92	1.18	1.56	2.55	dB	0.085

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.2 dB
Loss due to Connector 2:	0.2 dB
Base Weight:	0.042 pounds
Additional Weight per Inch:	0.00117 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.028 lbs [12.7 g]

Cable

Cable Type	RG316-DS
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.114 in [2.9 mm]
One Time Minimum Bend Radius	0.59 in [14.99 mm]
Repeated Minimum Bend Radius	1.57 in [39.88 mm]

SMB Plug Right Angle to SMB Plug Right Angle
Cable Using RG316-DS Coax with HeatShrink



PE3C0873/HS

Connectors

Description	Connector 1	Connector 2
Type	SMB Plug Right Angle	SMB Plug Right Angle
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	30µ in. minimum	30µ in. minimum
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100µ in. minimum	100µ in. minimum

Environmental Specifications

Operating Range Temperature -55 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMB Plug Right Angle to SMB Plug Right Angle Cable Using RG316-DS Coax with HeatShrink



PE3C0873/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3C0873/HS

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: PE3C0873/HS-12 = 12 inches long cable
PE3C0873/HS-100cm = 100 cm long cable

SMB Plug Right Angle to SMB Plug Right Angle Cable Using RG316-DS Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMB Plug Right Angle to SMB Plug Right Angle Cable Using RG316-DS Coax with HeatShrink PE3C0873/HS](#)

URL: <https://www.pasternack.com/smb-plug-right-angle-to-smb-plug-cable-using-rg316-ds-with-heatshrink-pe3c0873-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C0873/HS CAD Drawing

SMB Plug Right Angle to SMB Plug Right Angle Cable Using RG316-DS Coax with HeatShrink

