

QMA Male to Limited Detent SMP Male Bulkhead Cable Using RG405 Coax with HeatShrink



RF Cable Assemblies Technical Data Sheet

PE3C0874/HS

Configuration

- Connector 1: QMA Male
- Connector 2: Limited Detent SMP Male Bulkhead
- Cable Type: RG405

Features

- Shielding Effectivity > -110 dB
- 69.5% Phase Velocity

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C0874/HS QMA male to SMP male limited detent bulkhead cable using RG405 coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack QMA to SMP cable assembly has a male to male gender configuration with 50 ohm semi-rigid RG405 coax. Our RF cable assembly with SMP bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69.5		%
RF Shielding	-110			dB
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Weight 0.031 lbs [14.06 g]

Cable

Cable Type RG405
Impedance 50 Ohms
Inner Conductor Type Solid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [QMA Male to Limited Detent SMP Male Bulkhead Cable Using RG405 Coax with HeatShrink PE3C0874/HS](#)

**QMA Male to Limited Detent SMP Male Bulkhead
Cable Using RG405 Coax with HeatShrink**

RF Cable Assemblies Technical Data Sheet
PE3C0874/HS

Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Outer Conductor Material and Plating	Copper

Repeated Minimum Bend Radius	0.05 in [1.27 mm]
------------------------------	-------------------

Connectors

Description	Connector 1	Connector 2
Type	QMA Male	SMP Male Bulkhead
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Connection Method		Limited Detent
Mating Cycles		500
Contact Material and Plating	Gold	Brass, Gold
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold	Brass, Gold
Coupling Nut Material and Plating	Brass, Nickel	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [QMA Male to Limited Detent SMP Male Bulkhead Cable Using RG405 Coax with HeatShrink PE3C0874/HS](#)

QMA Male to Limited Detent SMP Male Bulkhead
Cable Using RG405 Coax with HeatShrink



RF Cable Assemblies Technical Data Sheet

PE3C0874/HS

How to Order

Part Number Configuration:

PE3C0874/HS - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C0874/HS-12 = 12 inches long cable
PE3C0874/HS-100cm = 100 cm long cable

QMA Male to Limited Detent SMP Male Bulkhead Cable Using RG405 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [QMA Male to Limited Detent SMP Male Bulkhead Cable Using RG405 Coax with HeatShrink PE3C0874/HS](#)

URL: <https://www.pasternack.com/qma-male-to-limited-detent-smp-male-bulkhead-cable-using-rg405-with-heatshrink-pe3c0874-hs-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C0874/HS CAD Drawing

QMA Male to Limited Detent SMP Male Bulkhead Cable

Using RG405 Coax with HeatShrink

		REVISION				
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY	
	A	INITIAL RELEASE	12/14/2022		AGANWANI	



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS , ONE LABEL APPROXIMATELY CENTERED, LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE