

2.92mm Male to SMP Female Cable Using PE-SR405FLJ Coax, RoHS

TECHNICAL DATA SHEET

PE3C0439

Configuration

Connector 1 2.92mm Male Connector 2 SMP Female Cable Type PE-SR405FLJ

Electrical Specifications

Frequency Range DC to 18 GHz 50 Ohms Impedance Maximum VSWR 1.35:1 Velocity of Propagation 69.5 % Group Delay 1.43 ns/ft [4.69 ns/m]

RF Shielding 100 dB Maximum Operating Voltage 1,500 Vrms

Mechanical Specifications

Temperature

Temperature Operating Range -55 to +125 deg C

Diameter 0.312 in [7.92 mm] Weight 0.035 lbs [15.88 g] Cable Color Black

One Time Minimum Bend Radius 0.236 in [5.99 mm] Repeated Minimum Bend Radius 0.787 in [19.99 mm]

Cable

PE-SR405FLJ Cable Type

Inner Conductor Type Solid

Cable Inner Conductor Copper Clad Steel, Silver

No of Shields **PTFE** Dielectric Type Jacket Material **FEP**

Jacket Diameter 0.098 in [2.49 mm]

Connector 1

Type 2.92mm Male Configuration Straight

Beryllium Copper, Gold Inner Conductor Material and Plating Inner Conductor Plating Specification 50µ in. minimum Coupling Nut Material and Plating Passivated Stainless Steel

Hex Size 5/16 in.

Torque 8 in-lbs [0.9 Nm] **Body Material and Plating** Beryllium Copper, Gold **Body Plating Specification** 50u in. minimum

Dielectric Type **PCTFE**

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Male to SMP Female Cable Using PE-SR405FLJ Coax, RoHS PE3C0439

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



OF TERMASK

2.92mm Male to SMP Female Cable Using PE-SR405FLJ Coax, RoHS

TECHNICAL DATA SHEET

PE3C0439

Connector 2

Type
Connector 2 Specification
Configuration
Inner Conductor Material and Plating
Inner Conductor Plating Specification
Outer Conductor Material and Plating
Body Material and Plating
Body Plating Specification
Dielectric Type

SMP Female DESC 94008 Straight Beryllium Copper, Gold MIL-G-45204 Beryllium Copper Beryllium Copper, Gold MIL-G-45204 Teflon

Compliance Certifications (visit www.Pasternack.com for current document)
RoHS Compliant
Yes

Plotted and Other Data

Notes:

• Values at +25 °C, sea level

2.92mm Male to SMP Female Cable Using PE-SR405FLJ Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Male to SMP Female Cable Using PE-SR405FLJ Coax, RoHS PE3C0439

URL: http://www.pasternack.com/2.92mm-male-smp-female-pe-sr405flj-cable-assembly-pe3c0439-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

