

SMA Female to MMCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink




PE3C0525/HS

Configuration

- Connector 1: SMA Female
- Connector 2: MMCX Plug Right Angle
- Cable Type: RG316-DS
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- Shielding Effectivity > 85 dB
- 69.5% Phase Velocity
- Double Shielded
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C0525/HS SMA female to MMCX plug right angle cable using RG316-DS coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to MMCX cable assembly has a female to plug gender configuration with 50 ohm flexible RG316-DS coax. The PE3C0525/HS SMA female to MMCX plug cable assembly operates to 3 GHz. The right angle MMCX interface on the RG316-DS cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 85 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
RF Shielding	85			dB
Capacitance		28.96 [95.01]		pF/ft [pF/m]
DC Resistance Inner Conductor		83.82 [275]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		5.33 [17.49]		Ohms/1000ft [Ohms/Km]

Specifications by Frequency

SMA Female to MMCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink



PE3C0525/HS

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			100	250	500	1000	3000	MHz	
PE3C0525/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.08	0.13	0.19	0.29	0.536	dB/ft	
			0.28	0.43	0.64	0.96	1.76	dB/m	
PE3C0525/HS-6	6 inch	Insertion Loss (Typ.)	0.35	0.37	0.4	0.45	0.57	dB	0.021
PE3C0525/HS-12	12 inch	Insertion Loss (Typ.)	0.39	0.43	0.5	0.59	0.84	dB	0.028
PE3C0525/HS-24	24 inch	Insertion Loss (Typ.)	0.47	0.56	0.69	0.88	1.38	dB	0.043
PE3C0525/HS-36	36 inch	Insertion Loss (Typ.)	0.55	0.69	0.89	1.17	1.91	dB	0.057
PE3C0525/HS-48	48 inch	Insertion Loss (Typ.)	0.64	0.82	1.08	1.46	2.45	dB	0.071

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.2 dB
Base Weight:	0.028 pounds
Additional Weight per Inch:	0.00117 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.014 lbs [6.35 g]

Cable

Cable Type	RG316-DS
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.114 in [2.9 mm]
One Time Minimum Bend Radius	0.59 in [14.99 mm]
Repeated Minimum Bend Radius	1.57 in [39.88 mm]

SMA Female to MMCX Plug Right Angle Cable
Using RG316-DS Coax with HeatShrink



PE3C0525/HS

Connectors

Description	Connector 1	Connector 2
Type	SMA Female	MMCX Plug Right Angle
Specification		BS EN 122340
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating		Brass, Gold
Contact Plating Specification		30μ in. minimum
Dielectric Type		Teflon
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification		3μ in. minimum

Environmental Specifications

Operating Range Temperature -55 to +155 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Female to MMCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink



PE3C0525/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3C0525/HS - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3C0525/HS-12 = 12 inches long cable
PE3C0525/HS-100cm = 100 cm long cable

SMA Female to MMCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to MMCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink PE3C0525/HS](#)

URL: <https://www.pasternack.com/sma-female-to-mmcx-plug-cable-using-rg316-ds-with-heatshrink-pe3c0525-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C0525/HS CAD Drawing

SMA Female to MMCX Plug Right Angle Cable Using RG316-DS Coax with HeatShrink

