

2.92mm Male to 2.92mm Male Low Loss Space Cable Using PE-R135LL Coax




PE3C100017

Configuration

- Connector 1: 2.92mm Male
- Connector 2: 2.92mm Male
- Cable Type: PE-R135LL
- Coax Flex Type: Flexible

Features

- Max Frequency 40 GHz
- Shielding Effectivity > 100 dB
- 82% Phase Velocity
- Double Shielded
- ETFE Jacket
- Up to 300 Mrad of Radiation Resistance
- Low Outgassing (TML <1%, CVCM <1%) per ASTM E-595
- Operating Temperature -65 to +150 Deg C
- Built in a Facility with < 100,000 Particles/sq ft
- Built to IPC-A-620 Class 3



Applications

- General Purpose
- Laboratory Use
- Vacuum Environments
- Low Earth Orbit (LEO)
- Space (Exploration, Launches, Maintenance, Stations)
- Ground Systems
- Satellites

Description

Pasternack's PE3C100017 2.92mm male to 2.92mm male cable using PE-R135LL coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 2.92mm to 2.92mm cable assembly has a male to male gender configuration with 50 ohm flexible PE-R135LL coax. The PE3C100017 2.92mm male to 2.92mm male cable assembly operates to 40 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 100 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.4:1	
Velocity of Propagation		82		%
RF Shielding	100			dB
Capacitance		25 [82.02]		pF/ft [pF/m]

Specifications by Frequency

2.92mm Male to 2.92mm Male Low Loss Space Cable Using PE-R135LL Coax



PE3C100017

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	2500	5000	10000	20000	40000	MHz	
PE3C100017	Custom Lengths Available	Insertion Loss (Typ.)	0.161	0.237	0.35	0.528	0.808	dB/ft	
			0.53	0.78	1.15	1.74	2.66	dB/m	
PE3C100017-12	12 Inch	Insertion Loss (Typ.)	0.37	0.44	0.55	0.73	1.01	dB	0.064
PE3C100017-18	18 Inch	Insertion Loss (Typ.)	0.45	0.56	0.73	1	1.42	dB	0.078
PE3C100017-24	24 Inch	Insertion Loss (Typ.)	0.53	0.68	0.9	1.26	1.82	dB	0.091
PE3C100017-100CM	100 CM	Insertion Loss (Typ.)	0.73	0.98	1.35	1.94	2.86	dB	0.124
PE3C100017-200CM	200 CM	Insertion Loss (Typ.)	1.26	1.76	2.5	3.67	5.51	dB	0.209

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB

Loss due to Connector 2: 0.1 dB

Base Weight: 0.064 pounds

Additional Weight per Inch: 0.00217 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.36 in [9.14 mm]
Weight	0.064 lbs [29.03 g]

Cable

Cable Type	PE-R135LL
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver plated copper
Shield Layer 2	Silver plated copper
Jacket Material	ETFE, Black
Jacket Diameter	0.145 in [3.68 mm]
One Time Minimum Bend Radius	1.08 in [27.43 mm]

Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male	2.92mm Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in minimum	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Stainless Steel, Passivated	Stainless Steel, Passivated

2.92mm Male to 2.92mm Male Low Loss Space Cable Using PE-R135LL Coax



PE3C100017

Environmental Specifications

Operating Range Temperature -65 to +150 deg C

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:
Values at 25°C, sea level.

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C100017-12 = 12 inches long cable
PE3C100017-100cm = 100 cm long cable

2.92mm Male to 2.92mm Male Low Loss Space Cable Using PE-R135LL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to 2.92mm Male Low Loss Space Cable Using PE-R135LL Coax PE3C100017](#)

URL: <https://www.pasternack.com/2.92mm-male-to-2.92mm-male-low-loss-space-cable-using-pe-r135ll-pe3c100017-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C100017 CAD Drawing

2.92mm Male to 2.92mm Male Low Loss Space Cable Using PE-R135LL Coax

