

3.5mm Female Bulkhead to TNC Male Right Angle Cable Using PE-SR402FL Coax

PE3C10084



Configuration

- Connector 1: 3.5mm Female Bulkhead
- Connector 2: TNC Male Right Angle
- Cable Type: PE-SR402FL
- Coax Flex Type: Formable

Features

- Shielding Effectivity > 110 dB
- 69.5% Phase Velocity



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C10084 3.5mm female bulkhead to TNC male right angle cable using PE-SR402FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack 3.5mm to TNC cable assembly has a female to male gender configuration with 50 ohm formable PE-SR402FL coax. The right angle TNC interface on the PE-SR402FL cable allows for easier connections in tight spaces. Our RF cable assembly with 3.5mm bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------------|---------|-------------|---------|-----------------------|
| Velocity of Propagation | | 69.5 | | % |
| RF Shielding | 110 | | | dB |
| Capacitance | | 29 [95.14] | | pF/ft [pF/m] |
| DC Resistance Inner Conductor | | 7.8 [25.59] | | Ohms/1000ft [Ohms/Km] |
| DC Resistance Outer Conductor | | 5.5 [18.04] | | Ohms/1000ft [Ohms/Km] |

Mechanical Specifications

Cable Assembly

Width/Diameter

0.5 in [12.7 mm]

Weight

0.083 lbs [37.65 g]

3.5mm Female Bulkhead to TNC Male Right Angle Cable Using PE-SR402FL Coax



PE3C10084

Cable

| | |
|--|---------------------|
| Cable Type | PE-SR402FL |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper, Silver |
| Dielectric Type | PTFE |
| Outer Conductor 1 Material and Plating | Tinned Copper Braid |
| Repeated Minimum Bend Radius | 0.625 in [15.88 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|-----------------------------------|----------------------------|-------------------------|
| Type | 3.5mm Female Bulkhead | TNC Male Right Angle |
| Impedance | 50 Ohms | 50 Ohms |
| Configuration | Straight | Right Angle |
| Contact Material and Plating | Gold | Brass, Gold over Nickel |
| Dielectric Type | PTFE | PTFE |
| Body Material and Plating | Passivated Stainless Steel | Brass, Nickel |
| Coupling Nut Material and Plating | | Brass, Nickel |

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

3.5mm Female Bulkhead to TNC Male Right Angle Cable Using PE-SR402FL Coax



PE3C10084

Typical Performance Data

How to Order

Part Number Configuration: **PE3C10084** **- xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3C10084-12 = 12 inches long cable
PE3C10084-100cm = 100 cm long cable

3.5mm Female Bulkhead to TNC Male Right Angle Cable Using PE-SR402FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3.5mm Female Bulkhead to TNC Male Right Angle Cable Using PE-SR402FL Coax PE3C10084](https://www.pasternack.com/3.5mm-female-bulkhead-to-tnc-male-cable-using-pe-sr402fl-pe3c10084-p.aspx)

URL: <https://www.pasternack.com/3.5mm-female-bulkhead-to-tnc-male-cable-using-pe-sr402fl-pe3c10084-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C10084 CAD Drawing
3.5mm Female Bulkhead to TNC Male Right Angle Cable Using PE-SR402FL Coax

