

2.92mm Male to TNC Male Right Angle Cable Using PE-SR402FL Coax





PE3C10099

Configuration

- Connector 1: 2.92mm Male
- Connector 2: TNC Male Right Angle
- Cable Type: PE-SR402FL
- Coax Flex Type: Formable

Features

- Shielding Effectivity > 110 dB
- 69.5% Phase Velocity



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C10099 2.92mm male to TNC male right angle cable using PE-SR402FL coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack 2.92mm to TNC cable assembly has a male to male gender configuration with 50 ohm formable PE-SR402FL coax. The right angle TNC interface on the PE-SR402FL cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69.5		%
RF Shielding	110			dB
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		7.8 [25.59]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		5.5 [18.04]		Ohms/1000ft [Ohms/Km]

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.076 lbs [34.47 g]

Cable

Cable Type	PE-SR402FL
------------	------------

2.92mm Male to TNC Male Right Angle Cable Using PE-SR402FL Coax



PE3C10099

Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Outer Conductor 1 Material and Plating	Tinned Copper Braid
Repeated Minimum Bend Radius	0.625 in [15.88 mm]

Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male	TNC Male Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Brass, Gold over Nickel
Contact Plating Specification	50 μ in minimum	
Dielectric Type	PCTFE	PTFE
Body Material and Plating	Stainless Steel, Gold over Nickel	Brass, Nickel
Body Plating Specification	50 μ in minimum	
Coupling Nut Material and Plating	Stainless Steel, Gold over Nickel	Brass, Nickel
Coupling Nut Plating Specification	50 μ in minimum	
Hex Size	5/16 inch	
Torque	8 in-lbs 0.9 Nm	

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2.92mm Male to TNC Male Right Angle Cable Using PE-SR402FL Coax




PE3C10099

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C10099-12 = 12 inches long cable
PE3C10099-100cm = 100 cm long cable

2.92mm Male to TNC Male Right Angle Cable Using PE-SR402FL Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to TNC Male Right Angle Cable Using PE-SR402FL Coax PE3C10099](#)

URL: <https://www.pasternack.com/2.92mm-male-to-tnc-male-cable-using-pe-sr402fl-pe3c10099-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C10099 CAD Drawing

2.92mm Male to TNC Male Right Angle Cable Using PE-SR402FL Coax

