

SSMA Male to SSMC Plug Low Loss Cable Using LMR-100A-UF Coax with HeatShrink

PE3C10163/HS




Configuration

- Connector 1: SSMA Male
- Connector 2: SSMC Plug
- Cable Type: LMR-100A-UF
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- Double Shielded
- TPE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C10163/HS SSMA male to SSMC plug cable using LMR-100A-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SSMA to SSMC cable assembly has a male to plug gender configuration with 50 ohm flexible LMR-100A-UF coax. The PE3C10163/HS SSMA male to SSMC plug cable assembly operates to 3 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
RF Shielding	90			dB
Group Delay		1.54 [5.05]		ns/ft [ns/m]
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Inductance		0.077 [0.25]		uH/ft [uH/m]
DC Resistance Inner Conductor		81 [265.75]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		9.5 [31.17]		Ohms/1000ft [Ohms/Km]

SSMA Male to SSMC Plug Low Loss Cable Using LMR-100A-UF Coax with HeatShrink



PE3C10163/HS

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			2,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	3000	MHz	
PE3C10163/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.07	0.115	0.166	0.24	0.435	dB/ft	
			0.23	0.38	0.55	0.79	1.43	dB/m	
PE3C10163/HS-24	24 In	Insertion Loss (Typ.)	0.34	0.43	0.54	0.68	1.07	dB	0.031
PE3C10163/HS-36	36 In	Insertion Loss (Typ.)	0.41	0.55	0.7	0.92	1.51	dB	0.039
PE3C10163/HS-48	48 In	Insertion Loss (Typ.)	0.48	0.66	0.87	1.16	1.94	dB	0.047
PE3C10163/HS-100CM	100 CM	Insertion Loss (Typ.)	0.43	0.58	0.75	0.99	1.63	dB	0.041
PE3C10163/HS-200CM	200 CM	Insertion Loss (Typ.)	0.66	0.96	1.29	1.78	3.06	dB	0.067

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.022 pounds
Additional Weight per Inch:	0.00067 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.0133 lbs [6.03 g]

Cable

Cable Type	LMR-100A-UF
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper
Jacket Material	TPE, Black
Jacket Diameter	0.11 in [2.79 mm]
One Time Minimum Bend Radius	0.25 in [6.35 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Bending Moment	0.1 lbs-ft [0.14 N-m]
Flat Plate Crush	10 lbs/in [0.18 Kg/mm]
Tensile Strength	15 lbs [6.8 Kg]

SSMA Male to SSMC Plug Low Loss Cable Using LMR-100A-UF Coax with HeatShrink



PE3C10163/HS

Connectors

Description	Connector 1	Connector 2
Type	SSMA Male	SSMC Plug
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles		500
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification	50 µin minimum	
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Beryllium Copper, Gold
Body Plating Specification	100 µin minimum	
Coupling Nut Material and Plating	Brass, Nickel	Beryllium Copper, Gold
Coupling Nut Plating Specification	100 µin minimum	
Hex Size	1/4 inch	5/32 inch
Torque	2 in-lbs 0.23 Nm	1 in-lbs 0.11 Nm

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SSMA Male to SSMC Plug Low Loss Cable Using LMR-100A-UF Coax with HeatShrink



PE3C10163/HS

Typical Performance Data

How to Order

Part Number Configuration: **PE3C10163/HS - xx uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3C10163/HS-12 = 12 inches long cable
PE3C10163/HS-100cm = 100 cm long cable

SSMA Male to SSMC Plug Low Loss Cable Using LMR-100A-UF Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SSMA Male to SSMC Plug Low Loss Cable Using LMR-100A-UF Coax with HeatShrink PE3C10163/HS](https://www.pasternack.com/ssma-male-to-ssmc-plug-low-loss-cable-using-lmr-100a-uf-with-heatshrink-pe3c10163-hs-p.aspx)

URL: <https://www.pasternack.com/ssma-male-to-ssmc-plug-low-loss-cable-using-lmr-100a-uf-with-heatshrink-pe3c10163-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C10163/HS CAD Drawing
SSMA Male to SSMC Plug Low Loss Cable Using LMR-100A-UF Coax with HeatShrink

