

Fire Rated N Male Right Angle to TNC Male Low Loss Cable Using TCOM-195-FR Coax With Times Microwave Components




PE3C10392

Configuration

- Connector 1: N Male Right Angle
- Connector 2: TNC Male
- Cable Type: TCOM-195-FR
- Coax Flex Type: Flexible

Features

- 80% Phase Velocity
- Triple Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C10392 type N male right angle to TNC male cable using TCOM-195-FR coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to TNC cable assembly has a male to male gender configuration with 50 ohm flexible TCOM-195-FR coax. The right angle type N interface on the TCOM-195-FR cable allows for easier connections in tight spaces. The triple shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		80		%
Group Delay		1.27 [4.17]		ns/ft [ns/m]
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.16 [23.49]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.42 [11.22]		Ohms/1000ft [Ohms/Km]
Jacket Spark			3,000	Vrms

Mechanical Specifications

Cable Assembly

Width/Diameter

0.5 in [12.7 mm]

Fire Rated N Male Right Angle to TNC Male Low Loss Cable Using TCOM-195-FR Coax With Times Microwave Components



PE3C10392

Weight 0.169 lbs [76.66 g]

Cable

Cable Type	TCOM-195-FR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	3
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male Right Angle	TNC Male
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Mating Cycles	500	
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification	50µ in. minimum	
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Tri-Metal	Brass, Silver
Body Plating Specification	80µ in. minimum	
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Silver
Coupling Nut Plating Specification	80µ in. minimum	
Hex Size	30	

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Fire Rated N Male Right Angle to TNC Male
Low Loss Cable Using TCOM-195-FR Coax
With Times Microwave Components




PE3C10392

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C10392-12 = 12 inches long cable
PE3C10392-100cm = 100 cm long cable

Fire Rated N Male Right Angle to TNC Male Low Loss Cable Using TCOM-195-FR Coax With Times Microwave Components from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fire Rated N Male Right Angle to TNC Male Low Loss Cable Using TCOM-195-FR Coax With Times Microwave Components PE3C10392](#)

URL: <https://www.pasternack.com/fire-rated-n-male-right-angle-to-tnc-male-low-loss-cable-using-tcom-195-fr-pe3c10392-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C10392 CAD Drawing

Fire Rated N Male Right Angle to TNC Male Low Loss Cable Using TCOM-195-FR Coax With Times Microwave Components

