
1.85mm Male to SSMC Plug Right Angle Cable Using PE-SR405FLJ Coax



PE3C10777

Configuration

- Connector 1: 1.85mm Male
- Connector 2: SSMC Plug Right Angle
- Cable Type: PE-SR405FLJ
- Coax Flex Type: Formable



Features

- Max Frequency 10 GHz
- Shielding Effectivity > 100 dB
- 69.5% Phase Velocity
- FEP Jacket
- 500 Mating Cycles

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C10777 1.85mm male to SSMC plug right angle cable using PE-SR405FLJ coax is part of our full line of RF components available for same-day shipping. Pasternack's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. This Pasternack 1.85mm to SSMC cable assembly has a male to plug gender configuration with 50 ohm formable PE-SR405FLJ coax. The PE3C10777 1.85mm male to SSMC plug cable assembly operates to 10 GHz. The right angle SSMC interface on the PE-SR405FLJ cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	GHz
VSWR			1.4:1	
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]
DC Resistance Inner Conductor		65.7 [215.55]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		10.2 [33.46]		Ohms/1000ft [Ohms/Km]
Operating Voltage (AC)			250	Vrms

Specifications by Frequency

© 2025 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.
+1 (866) 558-2786 | sales@pasternack.com | pasternack.com

1.85mm Male to SSMC Plug Right Angle Cable Using PE-SR405FLJ Coax



PE3C10777

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	500	1000	2500	5000	10000	MHz	
PE3C10777	Custom Lengths Available	Insertion Loss (Typ.)	0.15	0.225	0.346	0.549	0.812	dB/ft	
			0.5	0.74	1.14	1.81	2.67	dB/m	
PE3C10777-6	6 In	Insertion Loss (Typ.)	0.31	0.36	0.44	0.57	0.74	dB	0.03
PE3C10777-9	9 In	Insertion Loss (Typ.)	0.35	0.41	0.53	0.71	0.94	dB	0.035
PE3C10777-12	12 In	Insertion Loss (Typ.)	0.38	0.47	0.61	0.84	1.14	dB	0.04
PE3C10777-18	18 In	Insertion Loss (Typ.)	0.46	0.58	0.79	1.12	1.55	dB	0.051
PE3C10777-24	24 In	Insertion Loss (Typ.)	0.53	0.69	0.96	1.39	1.96	dB	0.061

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.04*SQRT(FGHz)	dB
Loss due to Connector 2:	0.2	dB
Base Weight:	0.04	pounds
Additional Weight per Inch:	0.00167	pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.04 lbs [18.14 g]

Cable

Cable Type	PE-SR405FLJ
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor 1 Material and Plating	Tinned Copper Composite Braid
Jacket Material	FEP, Black
Jacket Diameter	0.105 in [2.67 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	0.787 in [19.99 mm]

© 2025 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.

1.85mm Male to SSMC Plug Right Angle Cable Using PE-SR405FLJ Coax



PE3C10777

Connectors

Description	Connector 1	Connector 2
Type	1.85mm Male	SSMC Plug Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Mating Cycles	500	500
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold
Contact Plating Specification	50 µin minimum	MIL-G-45204
Dielectric Type	PEI	Teflon
Body Material and Plating	Beryllium Copper, Gold over Nickel	Brass, Gold
Body Plating Specification	50 µin minimum	MIL-G-45204
Coupling Nut Material and Plating	Passivated Stainless Steel	Beryllium Copper, Gold
Coupling Nut Plating Specification	ASTM-A582	MIL-G-45204
Hex Size	5/16 inch	
Torque	8 in-lbs 0.9 Nm	1.75 in-lbs 0.2 Nm

Environmental Specifications

Operating Range Temperature	-55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

© 2025 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.
+1 (866) 558-2786 | sales@pasternack.com | pasternack.com

1.85mm Male to SSMC Plug Right Angle Cable Using PE-SR405FLJ Coax



PE3C10777

Typical Performance Data

How to Order

Part Number Configuration: **PE3C10777 - xx uu**

- uu — Unit of Measure:
  - cm = Centimeters
  - <blank> = Inches
- xx — Length
- PE3C10777 — Base Number

Example: PE3C10777-12 = 12 inches long cable
PE3C10777-100cm = 100 cm long cable

1.85mm Male to SSMC Plug Right Angle Cable Using PE-SR405FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.85mm Male to SSMC Plug Right Angle Cable Using PE-SR405FLJ Coax PE3C10777


URL: https://www.pasternack.com/1.85mm-male-to-ssmc-plug-cable-using-pe-sr405flj-pe3c10777-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

© 2025 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.

PE3C10777 CAD Drawing

1.85mm Male to SSMC Plug Right Angle Cable Using PE-SR405FLJ Coax



© 2025 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.