

SMA Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax



PE3C10852

Configuration

- Connector 1: SMA Male
- Connector 2: SMP Female Right Angle
- Cable Type: PE-SR047-NM
- Coax Flex Type: Semi-Rigid

Features

- Max Frequency 12.4 GHz
- Shielding Effectivity > 165 dB
- 69.5% Phase Velocity

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C10852 SMA male to SMP female right angle cable using PE-SR047-NM coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack SMA to SMP cable assembly has a male to female gender configuration with 50 ohm semi-rigid PE-SR047-NM coax. The PE3C10852 SMA male to SMP female cable assembly operates to 12.4 GHz. The right angle SMP interface on the PE-SR047-NM cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR			1.7:1	
Velocity of Propagation		69.5		%
RF Shielding	165			dB

Specifications by Frequency

SMA Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax



PE3C10852

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency		500	1000	2500		
PE3C10852	Custom Lengths Available	Insertion Loss (Typ.)	0.24	0.34	0.508	0.79	1.266	dB/ft	
			0.79	1.12	1.67	2.6	4.16	dB/m	
PE3C10852-6	6 inch	Insertion Loss (Typ.)	0.27	0.32	0.43	0.59	0.86	dB	0.104
PE3C10852-9	9 inch	Insertion Loss (Typ.)	0.33	0.41	0.55	0.78	1.18	dB	0.105
PE3C10852-12	12 inch	Insertion Loss (Typ.)	0.39	0.49	0.68	0.98	1.5	dB	0.106
PE3C10852-18	18 inch	Insertion Loss (Typ.)	0.51	0.66	0.93	1.38	2.13	dB	0.109
PE3C10852-24	24 inch	Insertion Loss (Typ.)	0.63	0.83	1.19	1.77	2.76	dB	0.111

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.12 dB
Loss due to Connector 2:	0.03*SQRT(FGHz) dB
Base Weight:	0.106 pounds
Additional Weight per Inch:	0.00034 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.106 lbs [48.08 g]

Cable

Cable Type	PE-SR047-NM
Impedance	50 Ohms
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Outer Conductor 1 Material and Plating	Copper
One Time Minimum Bend Radius	0.05 in [1.27 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	SMP Female Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Mating Cycles		500
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold over Copper
Dielectric Type	PTFE	
Body Material and Plating	Beryllium Copper, Gold	Bronze, Copper-Tin-Zinc Alloy over Silver
Coupling Nut Material and Plating	Beryllium Copper, Gold	
Torque	7 in-lbs 0.79 Nm	

SMA Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax



PE3C10852

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)


Plotted and Other Data

Notes:

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C10852-12 = 12 inches long cable
PE3C10852-100cm = 100 cm long cable

SMA Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax PE3C10852](#)

URL: <https://www.pasternack.com/sma-male-to-smp-female-non-magnetic-cable-using-pe-sr047-nm-pe3c10852-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C10852 CAD Drawing

SMA Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax



REVISION		DATE	CHANGED BY	APPROVED
ZONE	REV	DESCRIPTION	TDUFRENE	SRAUTUS
	A	INITIAL RELEASE		

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES AND TRAILING DIMENSIONS ARE IN MILLIMETERS

TOLERANCES:
 .X = ±.2 (5)
 .XX = ±.02 (0.5)
 .XXX = ±.005 (0.13)

FRACTIONS:
 ± 1/32
 ANGLES ± 1°

CABLE LENGTH TOLERANCES:
 $12 [305] \le 60 [1524] = +2 [51] / -0$
 $60 [1524] \le 120 [3048] = +4 [102] / -0$
 $120 [3048] \le 300 [7620] = +5 [127] / -0$

ALL DIMENSIONS ARE FOR REFERENCE ONLY. UNDIMENSIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.

PE PASTERNAK
an INFINITE brand

Website: www.Pasternack.com
 Phone: 1.866.727.8376 | 1.949.261.1920

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE: NONE
SHEET: 1 OF 1

DESCRIPTION		SMA MALE TO SMP FEMALE RIGHT ANGLE NON-MAGNETIC CABLE USING PE-SR047-NM COAX	
SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	53919	TDUFRENE	PE3C10852

- NOTES:**
- CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SERVICES WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVISION CONTRARY TO U.S. LAW PROHIBITED.

PE DS Rev-04 Add2