

## 2.92mm Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax



### PE3C10853

#### Configuration

- Connector 1: 2.92mm Male
- Connector 2: SMP Female Right Angle
- Cable Type: PE-SR047-NM
- Coax Flex Type: Semi-Rigid

#### Features

- Max Frequency 12.4 GHz
- Shielding Effectivity > 165 dB
- 69.5% Phase Velocity

#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3C10853 2.92mm male to SMP female right angle cable using PE-SR047-NM coax is part of our full line of RF components available for same-day shipping. Pasternack's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. This Pasternack 2.92mm to SMP cable assembly has a male to female gender configuration with 50 ohm semi-rigid PE-SR047-NM coax. The PE3C10853 2.92mm male to SMP female cable assembly operates to 12.4 GHz. The right angle SMP interface on the PE-SR047-NM cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR			1.7:1	
Velocity of Propagation		69.5		%
RF Shielding	165			dB

#### Specifications by Frequency

## 2.92mm Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax



### PE3C10853

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
			Frequency						
PE3C10853	Custom Lengths Available	Insertion Loss (Typ.)	0.24	0.34	0.508	0.79	1.266	dB/ft	
			0.79	1.12	1.67	2.6	4.16	dB/m	
PE3C10853-6	6 inch	Insertion Loss (Typ.)	0.27	0.32	0.43	0.59	0.86	dB	0.104
PE3C10853-9	9 inch	Insertion Loss (Typ.)	0.33	0.41	0.55	0.78	1.18	dB	0.105
PE3C10853-12	12 inch	Insertion Loss (Typ.)	0.39	0.49	0.68	0.98	1.5	dB	0.106
PE3C10853-18	18 inch	Insertion Loss (Typ.)	0.51	0.66	0.93	1.38	2.13	dB	0.109
PE3C10853-24	24 inch	Insertion Loss (Typ.)	0.63	0.83	1.19	1.77	2.76	dB	0.111

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.12 dB
Loss due to Connector 2:	0.03*SQRT(FGHz) dB
Base Weight:	0.106 pounds
Additional Weight per Inch:	0.00034 pounds

### Mechanical Specifications

#### Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.106 lbs [48.08 g]

#### Cable

Cable Type	PE-SR047-NM
Impedance	50 Ohms
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Outer Conductor 1 Material and Plating	Copper
One Time Minimum Bend Radius	0.05 in [1.27 mm]

### Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male	SMP Female Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Right Angle
Mating Cycles		500
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold over Copper
Dielectric Type	PEI	
Body Material and Plating	Beryllium Copper, Gold	Bronze, Copper-Tin-Zinc Alloy over Silver
Coupling Nut Material and Plating	Beryllium Copper, Gold	

## 2.92mm Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax



### PE3C10853

#### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)


#### Plotted and Other Data

Notes:

#### Typical Performance Data

#### How to Order

Part Number Configuration:



Example: PE3C10853-12 = 12 inches long cable  
PE3C10853-100cm = 100 cm long cable

2.92mm Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax PE3C10853](#)

URL: <https://www.pasternack.com/2.92mm-male-to-smp-female-non-magnetic-cable-using-pe-sr047-nm-pe3c10853-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3C10853 CAD Drawing

2.92mm Male to SMP Female Right Angle Non-Magnetic Cable Using PE-SR047-NM Coax

