

TNC Male to SMA Male Cable 200 cm Length  
Using LMR-400-UF Coax with HeatShrink



RF Cable Assemblies Technical Data Sheet


PE3C1704/HS-200CM

**Configuration**

- Connector 1: TNC Male
- Connector 2: SMA Male
- Cable Type: LMR-400-UF

**Features**

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- Double Shielded
- TPE Jacket



**Applications**

- General Purpose
- Laboratory Use

**Description**

Pasternack's PE3C1704/HS-200CM TNC male to SMA male 200 cm cable using LMR-400-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to SMA cable assembly has a male to male gender configuration with 50 ohm flexible LMR-400-UF coax. The PE3C1704/HS-200CM TNC male to SMA male cable assembly operates to 5.8 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to SMA Male Cable 200 cm Length Using LMR-400-UF Coax with HeatShrink PE3C1704/HS-200CM](#)



## TNC Male to SMA Male Cable 200 cm Length Using LMR-400-UF Coax with HeatShrink

### RF Cable Assemblies Technical Data Sheet

PE3C1704/HS-200CM

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.45:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.07 [3.51]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		1.65 [5.41]		Ω/1000ft [Ω/Km]
Jacket Spark			8,000	Vrms

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Max.)	0.35	0.39	0.48	0.73	1.1	dB

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. Insertion Loss is estimated as 0.1 dB per connector.

#### Mechanical Specifications

##### Cable Assembly

Length*	78.74 in [200 cm]
Diameter	0.622 in [15.8 mm]

##### Cable

Cable Type	LMR-400-UF
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	TPE, Black
Jacket Diameter	0.405 in [10.29 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to SMA Male Cable 200 cm Length Using LMR-400-UF Coax with HeatShrink PE3C1704/HS-200CM](#)



## TNC Male to SMA Male Cable 200 cm Length Using LMR-400-UF Coax with HeatShrink

### RF Cable Assemblies Technical Data Sheet

PE3C1704/HS-200CM

One Time Minimum Bend Radius	1 in [25.4 mm]
Repeated Minimum Bend Radius	4 in [101.6 mm]
Bending Moment	0.38 lbs-ft [0.52 N-m]
Flat Plate Crush	20 lbs/in [0.36 Kg/mm]
Tensile Strength	160 lbs [72.57 Kg]

#### Connectors

Description	Connector 1	Connector 2
Type	TNC Male	SMA Male
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification		50 $\mu$ " Min
Dielectric Type		Teflon
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to SMA Male Cable 200 cm Length Using LMR-400-UF Coax with HeatShrink PE3C1704/HS-200CM](#)

TNC Male to SMA Male Cable 200 cm Length  
Using LMR-400-UF Coax with HeatShrink




RF Cable Assemblies Technical Data Sheet

PE3C1704/HS-200CM

**How to Order**

Part Number Configuration:



Example: PE3C1704/HS-12 = 12 inches long cable  
PE3C1704/HS-100cm = 100 cm long cable

TNC Male to SMA Male Cable 200 cm Length Using LMR-400-UF Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to SMA Male Cable 200 cm Length Using LMR-400-UF Coax with HeatShrink PE3C1704/HS-200CM](#)


URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C1704/HS-200CM CAD Drawing

TNC Male to SMA Male Cable 200 cm Length Using LMR-400-UF Coax with HeatShrink

REVISIONS					
REV.	DESCRIPTION	DATE	APPROVED		
A	INITIAL RELEASE	8/24/2020	S.SELLS		



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS		TOLERANCES:		THIRD-ANGLE PROJECTION	
X = ± 2	[.08]	FRACTIONS	± 1/32	THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION ALL RIGHTS RESERVED.	
XXX = ± .02	[.51]	ANGLES ± 1°			
XXX = ± .005	[.13]	CABLE LENGTH (L) TOLERANCES:			
L ≤ 12 [305] = +1 [25] / -0		L ≤ 12 [305] = +1 [25] / -0			
12 [305] < L ≤ 60 [1524] = +2 [51] / -0		60 [1524] < L ≤ 120 [3048] = +4 [102] / -0			
120 [3048] < L ≤ 300 [7620] = +6 [153] / -0		300 [7620] < L = +5% L / -0			
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.					

**PASTERNAK**  
an INFINITE brand

Pasterнак Enterprises, Inc.  
P.O. Box 16759, Irvine, CA 92623.  
Phone: 1.949.261.9200 | 1.866.727.8376  
Fax: 1.949.261.7451  
Website: [www.pasterнак.com](http://www.pasterнак.com)  
E-mail: [sales@pasterнак.com](mailto:sales@pasterнак.com)

SCALE 1 OF 1  
ITEM NO. PE3C1704/HS  
DRAWN BY K.DANG  
CAGE CODE 53919  
SIZE A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE  
WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.