



N Male to N Male Low Loss Cable Using LMR-600-DB Coax

TECHNICAL DATA SHEET


PE3C1548

Configuration

- Connector 1: N Male
- Connector 2: N Male
- Cable Type: LMR-600-DB
- Coax Flex Type: Flexible

Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 87% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C1548 type N male to type N male cable using LMR-600-DB coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to type N cable assembly has a male to male gender configuration with 50 ohm flexible LMR-600-DB coax. The PE3C1548 type N male to type N male cable assembly operates to 5.8 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Low Loss Cable Using LMR-600-DB Coax PE3C1548](#)



N Male to N Male Low Loss Cable Using LMR-600-DB Coax

TECHNICAL DATA SHEET

PE3C1548

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------------|---------|--------------|---------|-----------------|
| Frequency Range | DC | | 5.8 | GHz |
| Velocity of Propagation | | 87 | | % |
| RF Shielding | 90 | | | dB |
| Group Delay | | 1.17 [3.84] | | ns/ft [ns/m] |
| Capacitance | | 23.4 [76.77] | | pF/ft [pF/m] |
| Inductance | | 0.058 [0.19] | | uH/ft [uH/m] |
| DC Resistance Inner Conductor | | 0.53 [1.74] | | Ω/1000ft [Ω/Km] |
| DC Resistance Outer Conductor | | 1.2 [3.94] | | Ω/1000ft [Ω/Km] |
| Jacket Spark | | | 8,000 | Vrms |

Specifications by Frequency

| Part Number | Length | Description | F1 | F2 | F3 | F4 | F5 | Units | Weight (lbs) |
|--------------|--------------------------|-----------------------|------|------|------|------|------|-------|--------------|
| | | Frequency | 250 | 500 | 1000 | 2500 | 5800 | MHz | |
| PE3C1548 | Custom Lengths Available | Insertion Loss (Typ.) | 0.01 | 0.02 | 0.03 | 0.04 | 0.07 | dB/ft | |
| | | | 0.04 | 0.06 | 0.09 | 0.15 | 0.24 | dB/m | |
| PE3C1548-12 | 12 inch | Insertion Loss (Typ.) | 0.22 | 0.22 | 0.23 | 0.25 | 0.28 | dB | 0.434 |
| PE3C1548-36 | 36 inch | Insertion Loss (Typ.) | 0.24 | 0.26 | 0.28 | 0.34 | 0.42 | dB | 0.707 |
| PE3C1548-48 | 48 inch | Insertion Loss (Typ.) | 0.25 | 0.27 | 0.31 | 0.38 | 0.5 | dB | 0.843 |
| PE3C1548-180 | 180 inch | Insertion Loss (Typ.) | 0.38 | 0.46 | 0.59 | 0.86 | 1.3 | dB | 2.34 |
| PE3C1548-240 | 240 inch | Insertion Loss (Typ.) | 0.44 | 0.54 | 0.72 | 1.08 | 1.66 | dB | 3.02 |

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB

Loss due to Connector 2: 0.1 dB

Base Weight: 0.434 pounds

Additional Weight per Inch: 0.01134 pounds

Mechanical Specifications

Cable Assembly

Weight 0.434 lbs [196.86 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Low Loss Cable Using LMR-600-DB Coax PE3C1548](#)



N Male to N Male Low Loss Cable Using LMR-600-DB Coax

TECHNICAL DATA SHEET

PE3C1548

Cable

| | |
|--------------------------------------|----------------------|
| Cable Type | LMR-600-DB |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper Clad Aluminum |
| Dielectric Type | PE (F) |
| Number of Shields | 2 |
| Shield Layer 1 | Aluminum Tape |
| Shield Layer 2 | Tinned Copper Braid |
| Jacket Material | PE, Black |
| Jacket Diameter | 0.59 in [14.99 mm] |

| | |
|------------------------------|------------------------|
| One Time Minimum Bend Radius | 1.5 in [38.1 mm] |
| Repeated Minimum Bend Radius | 6 in [152.4 mm] |
| Bending Moment | 2.75 lbs-ft [3.73 N-m] |
| Flat Plate Crush | 60 lbs/in [1.07 Kg/mm] |
| Tensile Strength | 350 lbs [158.76 Kg] |

Connectors

| Description | Connector 1 | Connector 2 |
|-----------------------------------|------------------|------------------|
| Type | N Male Threaded | N Male Threaded |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material and Plating | Brass, Gold | Brass, Gold |
| Dielectric Type | PTFE | PTFE |
| Body Material and Plating | Brass, Tri-Metal | Brass, Tri-Metal |
| Coupling Nut Material and Plating | Brass, Tri-Metal | Brass, Tri-Metal |

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Low Loss Cable Using LMR-600-DB Coax PE3C1548](#)



N Male to N Male Low Loss Cable Using LMR-600-DB Coax

TECHNICAL DATA SHEET

PE3C1548

How to Order

Part Number Configuration:

PE3C1548- **xx****uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C1548-12 = 12 inches long cable
PE3C1548-100cm = 100 cm long cable

N Male to N Male Low Loss Cable Using LMR-600-DB Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Low Loss Cable Using LMR-600-DB Coax PE3C1548](#)

URL: <https://www.pasternack.com/n-male-to-n-male-low-loss-cable-using-lmr-600-db-pe3c1548-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C1548 CAD Drawing

N Male to N Male Low Loss Cable Using LMR-600-DB Coax

