

## SMA Male Right Angle to Reverse Polarity SMA Plug Cable Using RG316-DS Coax with HeatShrink




### RF Cable Assemblies Technical Data Sheet

**PE3C1933/HS**


#### Configuration

- Connector 1: SMA Male Right Angle
- Connector 2: SMA Plug Reverse Polarity
- Cable Type: RG316-DS



#### Features

- Shielding Effectivity > 85 dB
- 69.5% Phase Velocity
- Double Shielded
- FEP Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3C1933/HS SMA male right angle to reverse polarity SMA plug cable using RG316-DS coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to reverse polarity SMA cable assembly has a male to plug gender configuration with 50 ohm flexible RG316-DS coax. The right angle SMA interface on the RG316-DS cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 85 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		69.5		%
RF Shielding	85			dB
Capacitance		28.96 [95.01]		pF/ft [pF/m]
DC Resistance Inner Conductor		83.82 [275]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		5.33 [17.49]		Ω/1000ft [Ω/Km]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to Reverse Polarity SMA Plug Cable Using RG316-DS Coax with Heat-Shrink PE3C1933/HS](#)

## SMA Male Right Angle to Reverse Polarity SMA Plug Cable Using RG316-DS Coax with HeatShrink



### RF Cable Assemblies Technical Data Sheet

**PE3C1933/HS**

#### Mechanical Specifications

##### Cable Assembly

Weight	0.038 lbs [17.24 g]
<b>Cable</b>	
Cable Type	RG316-DS
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Tan
Jacket Diameter	0.114 in [2.9 mm]
One Time Minimum Bend Radius	0.59 in [14.99 mm]
Repeated Minimum Bend Radius	1.57 in [39.88 mm]

##### Connectors

Description	Connector 1	Connector 2
Type	SMA Male Right Angle	SMA Plug Reverse Polarity
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Gold
Contact Plating Specification	50 $\mu$ in minimum	
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 $\mu$ in minimum	
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 $\mu$ in minimum	
Hex Size	16-May inch	16-May in
Torque	3 in-lbs [0.34 Nm]	5 in-lbs [0.57 Nm]

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to Reverse Polarity SMA Plug Cable Using RG316-DS Coax with Heat-Shrink PE3C1933/HS](#)

SMA Male Right Angle to Reverse Polarity SMA Plug  
Cable Using RG316-DS Coax with HeatShrink



**RF Cable Assemblies Technical Data Sheet**

**PE3C1933/HS**

**How to Order**

Part Number Configuration:

**PE3C1933/HS - xx uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C1933/HS-12 = 12 inches long cable  
PE3C1933/HS-100cm = 100 cm long cable

SMA Male Right Angle to Reverse Polarity SMA Plug Cable Using RG316-DS Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to Reverse Polarity SMA Plug Cable Using RG316-DS Coax with HeatShrink PE3C1933/HS](#)


URL: <https://www.pasternack.com/sma-male-right-angle-to-reverse-polarity-sma-plug-cable-using-rg316-ds-with-heatshrink-pe3c1933-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C1933/HS CAD Drawing

## SMA Male Right Angle to Reverse Polarity SMA Plug Cable Using RG316-DS Coax with HeatShrink

ZONE	REV.	DESCRIPTION	REVISION	DATE	CHANGED BY	APPROVED BY
A		INITIAL RELEASE		01/20/2023	DAZINN	AGANIMANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT:  
36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED  
LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6  
FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE, WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.

<b>PASTERNACK</b> an INFINIT <sup>®</sup> brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5		REV A
TOLERANCES: $X = \pm 2$ [5] $.XX = \pm 02$ [.5] $.XXX = \pm 005$ [.13]		FRACTIONS $\pm 1/32$ ANGLES $\pm 1^\circ$ CABLE LENGTH TOLERANCES	SCALE SHEET	
		Website: <a href="http://www.Pasternack.com">www.Pasternack.com</a> Phone: 1.866.727.8376   1.949.261.1920	NONE 1 OF 1	
DESCRIPTION		<b>SMA MALE RIGHT ANGLE TO REVERSE POLARITY SMA PLUG CABLE USING RG316-DS COAX WITH HEATSHRINK</b>		
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS	SIZE A	CAGE CODE 53919	DRAWN BY DZINN	ITEM NO. PE3C1933/HS
<small>ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.</small>				