



Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle
Flexible Cable 60 Inch Length Using RG174 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet


PE3C1966/HS-60

Configuration

- Connector 1: FAKRA Jack Right Angle
- Connector 2: FAKRA Jack Right Angle
- Cable Type: RG174

Features

- Max Frequency 1 GHz
- 66% Phase Velocity
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C1966/HS-60 water blue FAKRA jack right angle to FAKRA jack right angle 60 inch cable using RG174 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack FAKRA to FAKRA cable assembly has a jack to jack gender configuration with 50 ohm flexible RG174 coax. The PE3C1966/HS-60 FAKRA jack to FAKRA jack cable assembly operates to 1 GHz. The right angle FAKRA interfaces on the RG174 cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle Flexible Cable 60 Inch Length Using RG174 Coax with HeatShrink PE3C1966/HS-60](#)



Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle
Flexible Cable 60 Inch Length Using RG174 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3C1966/HS-60

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		31.08 [101.97]		pF/ft [pF/m]
Input Power (Average)			17	Watts

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Typ.)	0.54	0.72	0.99	1.36	1.9	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.15dB per connector loss.

Mechanical Specifications

Cable Assembly

Length*	60 in [152.4 cm]
Diameter	0.37 in [9.4 mm]

Cable

Cable Type	RG174
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.11 in [2.79 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle Flexible Cable 60 Inch Length Using RG174 Coax with HeatShrink PE3C1966/HS-60](#)



Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle
Flexible Cable 60 Inch Length Using RG174 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3C1966/HS-60

Connectors

Description	Connector 1	Connector 2
Type	FAKRA Jack Right Angle	FAKRA Jack Right Angle
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Nickel	Brass, Nickel
Body Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle Flexible Cable 60 Inch Length Using RG174 Coax with HeatShrink PE3C1966/HS-60](#)



Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle
Flexible Cable 60 Inch Length Using RG174 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3C1966/HS-60

How to Order

Part Number Configuration:

PE3C1966/HS

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C1966/HS-12 = 12 inches long cable
PE3C1966/HS-100cm = 100 cm long cable

Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle Flexible Cable 60 Inch Length Using RG174 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle Flexible Cable 60 Inch Length Using RG174 Coax with HeatShrink PE3C1966/HS-60](https://www.pasternack.com/fakra-jack-fakra-jack-rg174au-cable-assembly-pe3c1966-hs-60-p.aspx)


URL: <https://www.pasternack.com/fakra-jack-fakra-jack-rg174au-cable-assembly-pe3c1966-hs-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C1966/HS-60 CAD Drawing

Water Blue FAKRA Jack Right Angle to FAKRA Jack Right Angle Flexible
Cable 60 Inch Length Using RG174 Coax with HeatShrink

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/14/2021	S.ELLIS



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
TOLERANCES:	
.X = ± .2 [5.08]	FRACTIONS ± 1/32
.XX = ± .02 [.51]	ANGLES ± 1°
.XXX = ± .005 [.13]	
CABLE LENGTH (L) TOLERANCES:	
L ≤ 12 [305] = +1 [25] / -0	
12 [305] < L ≤ 60 [1524] = +2 [51] / -0	
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	
120 [3048] < L ≤ 300 [7620] = +6 [152] / -0	
300 [7620] < L = +5% / -0	
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.	

PE PASTERNAK an INFINITI brand	
Pasternack Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.1920 1.866.727.8376 Fax: 1.949.261.7451 Website: www.pasternack.com E-mail: sales@pasternack.com	
SIZE	ITEM NO.
A	53919
DRAWN BY	K. DANG
REV	PE3C1966/HS
A	

THIRD-ANGLE PROJECTION	
THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION ALL RIGHTS RESERVED.	
SHEET	1 OF 1
SCALE	N/A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE
WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.