



Reverse Polarity TNC Plug to Reverse Polarity TNC Jack Low Loss Cable Using LMR-195 Coax

RF Cable Assemblies Technical Data Sheet


PE3C1994

Configuration

- Connector 1: TNC Plug Reverse Polarity
- Connector 2: TNC Jack Reverse Polarity
- Cable Type: LMR-195
- Coax Flex Type: Flexible

Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 80% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C1994 reverse polarity TNC plug to reverse polarity TNC jack cable using LMR-195 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity TNC to reverse polarity TNC cable assembly has a plug to jack gender configuration with 50 ohm flexible LMR-195 coax. The PE3C1994 reverse polarity TNC plug to reverse polarity TNC jack cable assembly operates to 5.8 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to Reverse Polarity TNC Jack Low Loss Cable Using LMR-195 Coax PE3C1994](#)



Reverse Polarity TNC Plug to Reverse Polarity TNC Jack Low Loss Cable Using LMR-195 Coax

RF Cable Assemblies Technical Data Sheet

PE3C1994

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		80		%
RF Shielding	90			dB
Group Delay		1.27 [4.17]		ns/ft [ns/m]
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.6 [24.93]		Ω /1000ft [Ω /Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ω /1000ft [Ω /Km]
Jacket Spark			3,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.057	0.081	0.116	0.19	0.299	dB/ft
	0.19	0.27	0.38	0.62	0.98	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.091 lbs [41.28 g]

Cable

Cable Type LMR-195
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper
 Dielectric Type PE (F)
 Number of Shields 2
 Shield Layer 1 Aluminum Tape
 Shield Layer 2 Tinned Copper Braid
 Jacket Material PE, Black
 Jacket Diameter 0.195 in [4.95 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to Reverse Polarity TNC Jack Low Loss Cable Using LMR-195 Coax PE3C1994](#)



Reverse Polarity TNC Plug to Reverse Polarity TNC Jack Low Loss Cable Using LMR-195 Coax

RF Cable Assemblies Technical Data Sheet

PE3C1994

One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

Connectors

Description	Connector 1	Connector 2
Type	TNC Plug Reverse Polarity	TNC Jack Reverse Polarity
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	100 µin minimum

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
-----------------	------------------

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to Reverse Polarity TNC Jack Low Loss Cable Using LMR-195 Coax PE3C1994](#)



Reverse Polarity TNC Plug to Reverse Polarity TNC Jack Low Loss Cable Using LMR-195 Coax

RF Cable Assemblies Technical Data Sheet

PE3C1994

How to Order

Part Number Configuration:

PE3C1994

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C1994-12 = 12 inches long cable
PE3C1994-100cm = 100 cm long cable

Reverse Polarity TNC Plug to Reverse Polarity TNC Jack Low Loss Cable Using LMR-195 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to Reverse Polarity TNC Jack Low Loss Cable Using LMR-195 Coax PE3C1994](#)

URL: <https://www.pasternack.com/reverse-polarity-tnc-plug-to-reverse-polarity-tnc-jack-low-loss-cable-using-lmr-195-pe3c1994-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C1994 CAD Drawing

Reverse Polarity TNC Plug to Reverse Polarity TNC Jack
Low Loss Cable Using LMR-195 Coax

