



## N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink

### TECHNICAL DATA SHEET


**PE3C2075/HS**

#### Configuration

- Connector 1: N Male
- Connector 2: N Male
- Cable Type: LMR-200
- Coax Flex Type: Flexible

#### Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 83% Phase Velocity
- Double Shielded
- PE Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3C2075/HS type N male to type N male cable using LMR-200 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to type N cable assembly has a male to male gender configuration with 50 ohm flexible LMR-200 coax. The PE3C2075/HS type N male to type N male cable assembly operates to 5.8 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink PE3C2075/HS](#)



## N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink

### TECHNICAL DATA SHEET

**PE3C2075/HS**

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		83		%
RF Shielding	90			dB
Group Delay		1.22 [4]		ns/ft [ns/m]
Capacitance		24.5 [80.38]		pF/ft [pF/m]
Inductance		0.061 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		5.36 [17.59]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ω/1000ft [Ω/Km]
Dielectric Withstanding Voltage (DC)		500		Vdc
Jacket Spark		3,000		Vrms

#### Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	5800	MHz	
PE3C2075/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.05	0.07	0.1	0.16	0.26	dB/ft	
			0.17	0.23	0.33	0.53	0.86	dB/m	
PE3C2075/HS-24	24 inch	Insertion Loss (Typ.)	0.6	0.64	0.7	0.82	1.02	dB	0.08
PE3C2075/HS-36	36 inch	Insertion Loss (Typ.)	0.65	0.71	0.8	0.98	1.28	dB	0.11
PE3C2075/HS-48	48 inch	Insertion Loss (Typ.)	0.7	0.78	0.9	1.14	1.54	dB	0.13
PE3C2075/HS-60	60 inch	Insertion Loss (Typ.)	0.75	0.85	1	1.3	1.8	dB	0.15
PE3C2075/HS-72	72 inch	Insertion Loss (Typ.)	0.8	0.92	1.1	1.46	2.06	dB	0.17

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.25 dB

Loss due to Connector 2: 0.25 dB

Base Weight: 0.061 pounds

Additional Weight per Inch: 0.00184 pounds

#### Mechanical Specifications

##### Cable Assembly

Weight 0.182 lbs [82.55 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink PE3C2075/HS](#)



## N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink

### TECHNICAL DATA SHEET

**PE3C2075/HS**
**Cable**

Cable Type	LMR-200
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]

One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

**Connectors**

Description	Connector 1	Connector 2
Type	N Male Threaded	N Male Threaded
Specification	MIL-STD-348	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal

**Environmental Specifications**
**Temperature**

Operating Range

-40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink PE3C2075/HS](#)



## N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink

### TECHNICAL DATA SHEET

**PE3C2075/HS**

#### How to Order

Part Number Configuration:

PE3C2075/HS - xx uu

Unit of Measure:  
cm = Centimeters  
<blank> = Inches

Length  
Base Number

Example: PE3C2075/HS-12 = 12 inches long cable  
PE3C2075/HS-100cm = 100 cm long cable

N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink PE3C2075/HS](#)

URL: <https://www.pasternack.com/n-male-to-n-male-low-loss-cable-using-lmr-200-with-heatshrink-pe3c2075-hs-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C2075/HS CAD Drawing

## N Male to N Male Low Loss Cable Using LMR-200 Coax with Solderless Times Microwave Components with HeatShrink

לְמִזְבֵּחַ תְּמִימָה תְּמִימָה תְּמִימָה תְּמִימָה תְּמִימָה

ZONE	REV	DESCRIPTION			DATE	CHANGED BY	APPROVED
		INITIAL RELEASE	REVISION	REVISION			
1	A				09/26/2023	DMAY	AGAMMANI



## NOTES.

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
- 2.
- 3.

 <b>PASTERNACK®</b> an INFINITI® brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE SHEET 1 OF 1	
<b>UNLESS OTHERWISE SPECIFIED,          LEADING DIMENSIONS IN [ ] ARE INCHES          DIMENSIONS IN [ ] ARE MILLIMETERS</b>			
<b>TOLERANCES:</b> $X = \pm 12.15$ $XX = \pm 0.02$ [0.13] $XXX = \pm 0.006$ [0.13]	<b>FRACTIONS</b> $\pm 1/32$ <b>ANGLES</b> $\pm 1^\circ$ <b>CABLE LENGTH TOLERANCES:</b>	<b>DESCRIPTION</b> <b>N MALE TO N MALE LOW LOSS CABLE USING LMR-200 COAX          WITH SOLDERLESS TIMES MICROWAVE COMPONENTS WITH          HEATSHRINK</b>	Website: <a href="http://www.Pasternack.com">www.Pasternack.com</a> Phone: 1.866.727.8376   1.949.261.1920
$X = \pm 12.15$ $XX = \pm 0.02$ [0.13]	$\leq 12 [305]$ $\leq 60 [1524]$ $\leq 120 [3048]$ $\leq 120 [3048]$ $>300 [7620]$	$\leq 12 [305]$ $\leq 60 [1524]$ $\leq 120 [3048]$ $\leq 120 [3048]$ $>300 [7620]$	$+1 [25]$ $+2 [51]$ $+4 [102]$ $+6 [152]$ $+5\% [-0]$
<b>ALL DIMENSIONS ARE FOR REFERENCE ONLY          AND SUBJECT TO CHANGE WITHOUT NOTICE          UN-DIMENSIONED NON-CRITICAL FEATURES          MAY VARY IN SIZE AND LOCATION          COLORS MAY VARY</b>		<b>SIZE</b> <b>A</b>	<b>ITEM NO.</b> <b>PE3C2075/HS</b>
<b>REV</b> <b>A</b>		<b>CAGE CODE</b> <b>53919</b>	<b>DRAWN BY</b> <b>DMAY</b>

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMITMENTS, TECHNICAL OR SOFTWARE, WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.