

N Male to TNC Male Low Loss Cable
300 Inch Length Using LMR-240-UF Coax With
Times Microwave Components with HeatShrink




PE3C2211/HS-300

Configuration

- Connector 1: N Male
- Connector 2: TNC Male
- Cable Type: LMR-240-UF
- Coax Flex Type: Flexible

Features

- Max Frequency 8 GHz
- 84% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C2211/HS-300 type N male to TNC male 300 inch cable using LMR-240-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to TNC cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240-UF coax. The PE3C2211/HS-300 type N male to TNC male cable assembly operates to 8 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		8	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
Capacitance		24.2 [79.4]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2	4	8	GHz
Insertion Loss (Typ.)	1.83	2.6	3.7	4.18	6.49	dB

N Male to TNC Male Low Loss Cable
300 Inch Length Using LMR-240-UF Coax With
Times Microwave Components with HeatShrink



PE3C2211/HS-300

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of $0.1 * \text{sqrt}(f\text{ghz})$ for the N male connector and 0.1 dB for the TNC male connector.

Mechanical Specifications

Cable Assembly

Length	300 in [762 cm]
Width/Diameter	0.5 in [12.7 mm]
Weight	0.939 lbs [425.92 g]

Cable

Cable Type	LMR-240-UF
Impedance	50 Ohms
Inner Conductor Type	Solid
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Tinned Copper
Shield Layer 2	Aluminum Tape
Jacket Material	PE, Black
One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male	TNC Male
Specification	MIL-STD-348	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications

(see product page for current document)

Plotted and Other Data

Notes:

N Male to TNC Male Low Loss Cable
300 Inch Length Using LMR-240-UF Coax With
Times Microwave Components with HeatShrink




PE3C2211/HS-300

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C2211/HS-12 = 12 inches long cable
PE3C2211/HS-100cm = 100 cm long cable

N Male to TNC Male Low Loss Cable 300 Inch Length Using LMR-240-UF Coax With Times Microwave Components with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to TNC Male Low Loss Cable 300 Inch Length Using LMR-240-UF Coax With Times Microwave Components with HeatShrink PE3C2211/HS-300](#)

URL: <https://www.pasternack.com/n-male-to-tnc-male-low-loss-cable-300-inch-length-using-lmr-240-uf-with-heatshrink-pe3c2211-hs-300-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C2211/HS-300 CAD Drawing

N Male to TNC Male Low Loss Cable 300 Inch Length Using LMR-240-UF Coax With Times Microwave Components with HeatShrink

