




RF Cable Assemblies Technical Data Sheet

PE3C3446-36



Description

Pasternack's PE3C3446-36 BNC male to BNC female bulkhead 36 inch cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack BNC to BNC cable assembly has a male to female gender configuration with 50 ohm flexible RG316 coax. The PE3C3446-36 BNC male to BNC female cable assembly operates to 1 GHz. Our RF cable assembly with BNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BNC Male to BNC Female Bulkhead Cable 36 Inch Length Using RG316 Coax PE3C3446-36

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3C3446-36

Electrical Specifications

Description	n	Minimu	ım Ty	pical	Maximum	Units
Frequency Range		DC			1,000	MHz
VSWR					1.4:1	
Velocity of Propagation				69		%
Capacitance			29.	4 [96.46]		pF/ft [pF/m]
DC Resistance Inner Condu	uctor		8.4	1 [27.59]		Ω/1000ft [Ω/Km]
Operating Voltage (AC)					335	Vrms
Jacket Spark					2,000	Vrms
Specifications by Fr	equency					
Specifications by Free Description	equency F1	F2	F3	F4	F5	Units
Specifications by Fro Description Frequency		F2 250	F3 500	F4 1,000	F5	Units MHz
Description	F1				F5	
Description Frequency	F1 100	250	500	1,000	F5	MHz
Description Frequency Insertion Loss (Max.)	F1 100 0.54	250 0.64	500 0.79	1,000 1.1	F5	MHz dB

Mechanical Specifications

Cable Assembly Length* Diameter

Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Jacket Material Jacket Diameter 36 in [914.4 mm] 0.689 in [17.5 mm] 0.1 lbs [45.36 g]

RG316 50 Ohms Stranded Copper Clad Steel, Silver PTFE 1 Silver Plated Copper Braid FEP, Tan 0.102 in [2.59 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BNC Male to BNC Female Bulkhead Cable 36 Inch Length Using RG316 Coax PE3C3446-36

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



RF Cable Assemblies Technical Data Sheet



PE3C3446-36

Connectors

Description	Connector 1	Connector 2
Туре	BNC Male	BNC Female Bulkhead
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	50µ in. minimum	30 µin minimum
Dielectric Type	Teflon	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100µ in. minimum	100 µin minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100µ in. minimum	

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8$ ", whichever is greater.

Environmental Specifications Temperature

Operating Range

-55 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BNC Male to BNC Female Bulkhead Cable 36 Inch Length Using RG316 Coax PE3C3446-36

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3C3446-36

How to Order PE3C3446 Part Number Configuration: - XX uu Unit of Measure: cm = Centimeters <blank> = Inches Length Base Number Example: PE3C3446-12 = 12 inches long cable PE3C3446-100cm = 100 cm long cable BNC Male to BNC Female Bulkhead Cable 36 Inch Length Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: BNC Male to BNC Female Bulkhead Cable 36 Inch Length Using RG316 Coax PE3C3446-36 URL: https://www.pasternack.com/bnc-male-bnc-female-rg316u-cable-assembly-pe3c3446-36-p.aspx The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2019 Pasternack Enterprises All Rights Reserved

PE3C3446-36 CAD Drawing BNC Male to BNC Female Bulkhead Cable 36 Inch Length Using RG316 Coax

